

The Strion LED HL is a compact, hand-held flashlight that provides maximum illumination with a wide beam that is ideal for searching a large area.



<p>High, medium, low and strobe:</p> <ul style="list-style-type: none"> <li>– High: 615 lumens; 12,000 candela; 219m beam; runs 1.25 hours</li> <li>– Medium: 320 lumens; 6,000 candela; 155m beam; runs 2.5 hours</li> <li>– Low: 160 lumens; 3,000 candela; 110m beam; runs 4.5 hours</li> <li>– Strobe for signaling or disorienting: runs 3 hours</li> </ul>
<p>Optimized electronics provide regulated intensity</p>

<p>IPX4 water-resistant; 2m impact resistance tested</p>
<p>5.90 in. (14.99 cm); 5.2 oz (148g)</p>
<p>Limited Lifetime Warranty          Visit <a href="http://streamlight.com">streamlight.com</a> for full warranty information</p>
<p>See reverse for system configurations</p>

Item #	Description
74761	Strion LED HL - 230V AC/12V DC – 2 holders
74752	Strion LED HL - 120V/100V AC/12V DC – 2 holders
74760	Strion LED HL - 230V AC/12V DC – 1 holder
74764	Strion LED HL - 240V AC/12V DC – 1 holder
74751	Strion LED HL - 120V/100V AC/12V DC – 1 holder
74755	Strion LED HL - 120V/100V AC/12V DC – 1 holder Clam
74753	Strion LED HL - 120V/100V AC
74509	Strion LED HL with Grip Ring - 120V/100V AC
74754	Strion LED HL - 12V DC
74778	Strion LED HL - 120V/100V/12V DC PiggyBack
74750	Strion LED HL (WITHOUT CHARGER)

