

SHOWA

717



Providing protection against abrasion, puncture and snags, SHOWA 717 is an unlined, 11 mil nitrile glove that is the go-to for resistance to a broad range of solvents, animal fats and other chemicals.

[FEATURES

- Unsupported, unlined 100% nitrile
- 11 mil thick
- Bisque grip
- 13" length

[BENEFITS

- Provides chemical resistance against a broad range of solvents, oils, animal fats and other chemicals
- Mechanical resistance
- Bisque finish grip makes wet work easier and safer
- Ergonomic design maximizes comfort

[INDUSTRY



Chemical



Janitorial

[IDEAL APPLICATIONS

- Chemical spray and treatment
- Coating preparation
- Laboratory, pharma & analysis
- Painting & spray workshops
- Washing & cleaning



TAA PRODUCTS

MATERIAL

- Unsupported

COATING

- chemical resistant
- Nitrile
- Water resistant

GRIP

- Bisque

STANDARDS

Cat. III



0321

EN 388:2016



2001X

EN ISO 374-1:2016/Type A



JKLOPT

EN ISO 374-5:2016



SHOWA

717



PACKAGING

- 12 Pair per polybag
- 12 Polybags per case
- 144 Pair per case



COLOUR

- Light Green



SIZES

- XS
- S
- M
- L
- XL
- XXL



THICKNESS

- 11 mil




[YOU MIGHT ALSO BE INTERESTED IN

SHOWA
747




MATERIAL
Unsupported
COATING
chemical
resistant

SHOWA
737



MATERIAL
Unsupported
COATING
chemical
resistant

SHOWA
730



MATERIAL
Cotton flock
COATING
chemical
resistant

SHOWA
727



MATERIAL
Unsupported
COATING
chemical
resistant

[USER INSTRUCTIONS

Protection against mechanical risks, with electrostatic properties. Do not use where there are chemical, electrical, thermal or entanglement risks. Wash at 40°C max. Performance levels as per standard EN388 retained after 3 washes, subject to variations linked to actual usage conditions. The performance levels apply to the coated surface only. Store in a dry place, away from the light. All clothing and shoes worn with the glove with electrostatic dissipation properties must also be designed taking the electrostatic risk into account.

[DISCLAIMER

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment. The manufacturer reserves the right to make any modifications it deems necessary.

Get in touch

SHOWA USA | 579 Edison Street - Menlo, GA 30731, USA

USA@SHOWAgroup.com

© SHOWA Group 2018 | All rights reserved