

ALL-PURPOSE SILICONE LUBRICANT



LU™ 206



Light Pressure Lubricant



Minimum - Maximum operational temperature range: Low -50°F (-46°C) High 550°F (288°C)



5% Silicone



Features Spray Anyway™ nozzle



HMIS Hazard Rating: Health (2) • Flammability (4) • Reactivity (0)

- Works from -50°F to 550°F
- Does not interfere with painting operations
- Compatible with most surfaces



PRESERVE. PROTECT. PREVENT.™

Sprayon® LU™ 206 All-Purpose Silicone Lubricant is an economical lubricant for applications where petroleum based products are not desired. This 5% silicone formula protects against air and moisture to retard oxidation and corrosion. It virtually eliminates friction and sticking to improve high-speed production. Leaves a long-lasting film that is compatible with most surfaces. Equipped with an extension tube for hard-to-reach areas.

USES

- Windows
- Rubber components
- Doors
- Plastic assemblies
- Drawers
- Dissimilar metals
- Hinges
- Sliding wood surfaces
- Springs
- Layout tables
- Leather
- Weatherstripping



LU206

© 2010 Sprayon® Products Made in U.S.A.

LUBRICANTS

APPLICATION

Maximum performance is achieved when the metal surfaces to be protected are clean, dry and free of rust, oil and mill scale. Product should be sprayed in a well ventilated area. Sprays best at room temperature (70F.) Shake well before using. Spray at a distance of 10" to 14" from surface.

PERFORMANCE

PLASTIC SAFE: Yes

TEMPERATURE RANGE:

LOW: -50°F

HIGH: 550°F

LOAD CAPACITY: Light

- Penetrant
- Water-Displacer
- Rust Inhibitor
- Eliminates sticking
- Improves high speed production
- Retards oxidation and corrosion

PHYSICAL

APPEARANCE: Clear liquid

ODOR: Slight solvent

PROPELLANT: Hydrocarbon

WT./GAL.: 5.43

SPECIFIC GRAVITY: 0.65

VISCOSITY: Medium

PAINTABLE: Yes

% VOC AEROSOL: 94.00%

V.O.C. COMPLIANT CALIFORNIA: Yes

V.O.C. COMPLIANT OTC STATES: Yes

FLAMMABLE: Yes

FLASH POINT: <0°F

HAZARD RATING: 2,4,0

SHELF LIFE: 3 years from date of manufacture

PACKAGING

Stock #: S00206

UPC Code: 0-75577-90206-4

Fill Wt.: 10 oz.

Per Case: 12

Carton Dimensions:

L 10-7/8" x W 8-3/16" x H 8"

RESOURCES

MSDS/EDS/PRODUCT

DATA SHEETS:

sprayon.com

CUSTOMER SERVICE:

1-800-777-2966

TECHNICAL INFORMATION:

1-800-251-2486

SHIPPING

Refer to section 14 of the material safety data sheet for proper transport information and labeling.



Distributed by:

PRESERVE. PROTECT. PREVENT.



Sprayon® Products

101 Prospect Ave. NW
Cleveland, OH 44115
Sprayon.com
1-800-777-2966

310-PDS-LU206