



Main

| | |
|---------------------------|-------------------------------------|
| Range of Product | Harmony 9001SK Harmony 9001K |
| Product or Component Type | Light block |
| Device short name | 9001K |
| Bulb base | BA 9s |
| Light block supply | Direct via integral transformer 6 V |

Complementary

| | |
|---------------------------|------------------------|
| Net Weight | 0.32 lb(US) (0.144 kg) |
| Light source | Incandescent |
| [Us] rated supply voltage | 120 V AC |

Environment

| | |
|---------------------------------------|--|
| Protective treatment | TC |
| Ambient Air Temperature for Storage | -40...158 °F (-40...70 °C) |
| Ambient air temperature for operation | -13...158 °F (-25...70 °C) |
| IP degree of protection | IP20 IEC 60529 |
| Standards | EN/IEC 60947-5-4 EN/IEC 60947-5-1 JIS C 4520 CSA C22.2 No 14 EN/IEC 60947-1 UL 508 JIS C 852 |
| Product Certifications | UL 508 NEMA |
| Electrical shock protection class | Class II IEC 61140 |
| Vibration resistance | 7 gn 2...500 Hz)IEC 60068-2-6 |
| Shock resistance | 50 gn IEC 60068-2-27 |

Ordering and shipping details

| | |
|-----------------------|-------------------------------|
| Category | 21435 - 9001 KM LIGHT MODULES |
| Discount Schedule | CS1 |
| GTIN | 3389110918588 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 5.28 oz (149.686 g) |
| Returnability | Yes |
| Country of origin | MX |

Packing Units

| | |
|------------------------------|------------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 1.80 in (4.572 cm) |
| Package 1 width | 2.20 in (5.588 cm) |
| Package 1 Length | 3.70 in (9.398 cm) |
| Unit Type of Package 2 | CAR |
| Number of Units in Package 2 | 24 |
| Package 2 Weight | 8.43 lb(US) (3.825 kg) |
| Package 2 Height | 5.91 in (15 cm) |
| Package 2 width | 15.75 in (40 cm) |
| Package 2 Length | 9.45 in (24 cm) |


Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Dimensions



e panel thickness: 1 to 6 mm / 0.04 to 0.24 in.