

SHOWA

# S-TEX 376

Durability meets comfort with SHOWA's cut-and-liquid resistant S-TEX 376. Engineered with Hagane Coil® technology with ANSI Cut Level A4, and naturally fits the anatomy of your hand for maximum precision.

## FEATURES

- Engineered Hagane Coil® technology
- ISO 13997: Level D - EN388 Cut resistance level 4
- Level A4 ANSI cut-resistance
- Double dipped, ¾ coated, with an extra foamed nitrile finish on palm
- 13 Gauge knitted liner
- Anatomical hand shape design
- Seamless knit
- Nitrile foam grip

## BENEFITS

- Excellent cut resistance performance
- Nitrile coating with a second foamed nitrile coating providing high abrasion resistance
- Protects the hand from oils, hydrocarbons, grease and abrasion, with long lasting grip performance under wet and oily conditions
- An ergonomically designed hand mould replicates the natural curvature of the human hand and thus reduces hand fatigue, increasing productivity and dexterity
- Seamless knitting gives no irritation
- Liquid-proof to end of coated area
- Optimal grip performance in wet & oily conditions

## INDUSTRY



Aerospace



Automotive



Construction



Engineering



Glass



Manufacturing



Mechanical

## IDEAL APPLICATIONS

- Light assembly of oil-coated pieces
- Steel fabrication
- Steel fixing
- Handling heavy equipment
- Handling glass and windows
- Bottling
- Canning
- HVAC



## MATERIAL

- Polyester
- Stainless steel

## COATING

- Foam nitrile
- Nitrile

## GRIP

- Foam

## STANDARDS



ANSI / ISEA 105-2016



ANSI / ISEA 105-2016



SHOWA

# S-TEX 376



## PACKAGING

- 12 Pair per polybag
- 6 Polybags per case
- 72 Pair per case



## SIZES

- S
- M
- L
- XL
- XXL



## COLOUR

- Gray/ blue coating & black palm



## [ YOU MIGHT ALSO BE INTERESTED IN

### SHOWA S-TEX 581



**MATERIAL**  
Kevlar  
**COATING**  
Foam nitrile

### SHOWA S-TEX 541



**MATERIAL**  
Polyester  
**COATING**  
Polyurethane

### SHOWA S-TEX 350



**MATERIAL**  
Polyester  
**COATING**  
Nitrile

### SHOWA 257



**MATERIAL**  
Aramid knit  
**COATING**  
Foam nitrile

## [ USER INSTRUCTIONS

Do not use where there are chemical, electrical, thermal or entanglement risks. Wash at 40°C max. Performance levels as per standard EN388 retained after 3 washes, subject to variations linked to actual usage conditions. The performance levels apply to the coated surface only. Store in a dry place, away from the light. Do not use where there are electrical, thermal or entanglement risks. Discard used gloves in compliance with local regulations. Permeation information does not reflect the actual duration of protection in the workplace due to other factors that may influence the performance. Store in a dry place, away from the light.

## [ DISCLAIMER

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment. The manufacturer reserves the right to make any modifications it deems necessary.

## Get in touch

SHOWA USA | 579 Edison Street - Menlo, GA 30731, USA

USA@SHOWAGroup.com

© SHOWA Group 2018 | All rights reserved