

Choice® 800

Cleanroom Laundered 100% Polyester Knit Wiper

It's Choice®. The value tiered category of wipers offering all the performance consistency of higher priced wipers. Best of all, Choice® is from Berkshire, the most trusted name in contamination control products. Which means quality you

can count on. What's more, Choice® is backed by the Berkshire Guarantee - your money back if our wiper fails to perform according to specifications.



Key Attributes

- 100% continuous filament knit polyester
- Knife cut edge for reduced scratching potential
- Laundered and packaged in ISO Class 4 (Class 10) cleanroom

Benefits

- Very low particles, fibers, ions and extractables
- High abrasion resistant
- Excellent absorbency
- Knife cut edge for reduced scratching potential on sensitive surfaces
- Chemically compatible with IPA, Acetone and other solvents

Environmental

- Complies with RoHS and Reach requirements

Other Choice Products:

- Choice® 900
- Choice® Edge
- Choice® 700

Applications

- Designed for use in ISO Class 4 and higher environments
- Fab suite construction
- CD and DVD manufacturing processes
- Stencil and other print roll cleaning applications
- Cleaning of medical device products
- Applying and removing cleaning and disinfecting solutions
- Steam autoclavable for aseptic environments

Technical Data

Attribute		Units	Value	Test Method
Basis Weight		g/m ²	130	TAPPI T-410
Caliper		μm	516	TAPPI T-411
Fibers	≥100μm	fibers/cm ²	0.20	IEST-RP.CC004.3, Sec 6.1.4 / Sec 6.2.2
Particles	≥0.5μm	x10 ³ /cm ²	1.3	IEST-RP.CC004.3, Sec 6.1.4 / Sec 6.2.1
Sorbency	Capacity	mL/m ²	392	IEST-RP.CC004.3, Sec 8.1 modified / Sec 8.2 modified
	Efficiency	mL/g	3.0	
	Rate	seconds	1	
Non-Volatile Residue	DI Water	g/m ²	0.0044	IEST-RP.CC004.3, Sec 7.1.2
	IPA	g/m ²	0.0089	
Ions	Na ⁺	ppm	0.014	IEST-RP.CC004.3, Sec 7.2.2
	K ⁺	ppm	0.0052	
	Ca ⁺⁺	ppm	0.025	
	Mg ⁺⁺	ppm	0.00037	
	Cl ⁻	ppm	0.014	

Notes:

- Technical data represented in this table are typical values at the time of publication. These should not be used as product specifications.
- Due to differences in test methods applied and equipment utilized by different wiper manufacturers, valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions
- Third party testing can be performed upon request

Order Information

Product	Number	Size	Shts/pk	Pks/cs
Choice® 800	CH809.10	9x9"(23x23cm)	150	10

Other Berkshire Products



Wipers




Mop Systems



Face Masks



Glove Liners



Documentation Systems



Swabs