

Previously known as: MICROCHEM® by AlphaTec® 2300 PLUS - Model 132

Lightweight and durable chemical protection against a range of inorganic chemicals and biological hazards.

- A good protective barrier to numerous inorganic liquid chemicals including acids and bases
- Type 3 coverall, lightweight, yet relatively strong and durable
- Designed to protect, typical coverall features include respirator fit hood and a zip flap with self-adhesive tape closure
- Highly visible bright yellow for improved worker safety
- Anti-static, tested according to EN 1149-5

Industries

- Oil and gas
- Industrial
- Food Processing

Applications

- Environmental clean-up and remediation
- Tank Cleaning
- Equipment maintenance and repair



2300 PLUS - Model 132

Medium duty chemical barrier, Type 3/4/5 protection

Previously known as: MICROCHEM® by AlphaTec® 2300 PLUS - Model 132

PRODUCT INFORMATION

Product Material	Polyethylene on bicomponent Polypropylene/Polyethylene Nonwoven
Design Features	Coverall, 3-piece hood, 2 way front zipper with re-sealable storm flap, finger loops. Elasticated hood, waist, wrists and ankles.
Seam Type	Stitched and Taped
Standards Overview	CE CATEGORY III (Type 3-B, Type 4-B, Type 5-B, EN 1073-2, EN 14126, EN 1149-5)
Product Reference	2300 PLUS - Model 132
Sizes	S-5XL (02-09)
Weight	65gsm

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306.
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2019 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.