

# Hospital Products


## 15 and 20 Ampere, 125 Volts




15A 125V  
NEMA 5-15R  
UL CSA  
0.5 HP




20A 125V  
NEMA 5-20R  
UL CSA  
1 HP




USB8300C5W




USB8200AC5W



HBL420HS



HBL415HI



HBL4API

Dimensions in Inches (mm)

### Hospital Grade ● USB Charger Type-C, Type A&C and Type A



Hospital Grade USB Charger Outlet: two Type-C port configurations, high power 5 Amp, 5 Volt USB output, Tamper-Resistant duplex receptacle, USB ports rated 10,000 cycles.

Description

Black  
Brown  
Gray  
Ivory  
Light Almond  
Red  
White

Color

Black  
Brown  
Gray  
Ivory  
Light Almond  
Red  
White

Catalog Number

USB8200C5BK  
USB8200C5  
USB8200C5GY  
USB8200C5I  
USB8200C5LA  
USB8200C5R  
USB8200C5W

USB8300C5BK  
USB8300C5  
USB8300C5GY  
USB8300C5I  
USB8300C5LA  
USB8300C5R  
USB8300C5W



Hospital Grade USB Charger Outlet: one Type A and one Type-C port configurations, high power 5 Amp, 5 Volt USB output, Tamper-Resistant duplex receptacle, USB ports rated 10,000 cycles.

Black  
Brown  
Gray  
Ivory  
Light Almond  
Red  
White

Black  
Brown  
Gray  
Ivory  
Light Almond  
Red  
White

USB8200AC5BK  
USB8200AC5  
USB8200AC5GY  
USB8200AC5I  
USB8200AC5LA  
USB8200AC5R  
USB8200AC5W



Hospital Grade USB Charger Outlet: two Type A port configurations, high power 5 Amp, 5 Volt USB output, Tamper-Resistant duplex receptacle, USB ports rated 10,000 cycles.

Black  
Brown  
Gray  
Ivory  
Light Almond  
Red  
White

Black  
Brown  
Gray  
Ivory  
Light Almond  
Red  
White

USB8300A5BK  
USB8300A5  
USB8300A5GY  
USB8300A5I  
USB8300A5LA  
USB8300A5R  
USB8300A5W

Note: See page A-7 for additional information on USB charger devices.

### 4-PLEX® Hospital Grade ● Receptacles



Description

4 outlet high impact resistant Polycarbonate construction. Mount to 4 in. square box.

Color

Brown  
Gray  
Ivory  
Red  
White

Catalog Number

HBL415H  
-  
HBL415HI  
HBL415HR  
HBL415HW

4-PLEX surge protection receptacles with lights, 80 joules, 6.5kA peak current.

Blue  
Ivory  
Red

-  
-  
-

HBL420HS  
HBL420HIS  
HBL420HRS

### 4-PLEX® Accessories

Description

4-PLEX adapter plates for 1- and 2-gang, device boxes.

Color

Brown  
Gray  
Ivory  
Red  
White

Catalog Number

HBL4AP  
HBL4APGY  
HBL4API  
HBL4APR  
HBL4APW

Note: See page A-28 for additional information on 4-PLEX devices.