

3M™ Rugged Comfort Half Facepiece Reusable Respirator 6500 Series



6500

Rugged Comfort

in the harshest environments



— INTRODUCING —

3M™ HALF FACEPIECE REUSABLE RESPIRATOR
6500 SERIES

The 3M™ Rugged Comfort Half Facepiece Reusable Respirator is designed with tough and dirty worksites in mind.

Stay productive and protected – the 6500 Series delivers comfort, durability and stability with a firm, lightly textured silicone face seal and strong body construction.



3M™ RUGGED COMFORT HALF FACEPIECE REUSABLE RESPIRATOR 6500

Rugged, Comfortable, Low Profile

Choose from two options: 6500 or 6500QL



Adjustable Head Harness Assembly

- Optimum fit and comfort with three-size adjustable head cradle
- Long-lasting polyester/spandex straps

Valve Cover Design

- Directs exhaled breath and moisture downward
- Easy positive pressure seal check

Quick Latch - Drop-Down Mechanism

- Easy on and off as you move in and out of contaminated areas
- No need to remove your hardhat or face shield when lowering or raising your respirator



3M™ Bayonet Connection

- Compatible with all bayonet-style 3M™ cartridges and filters

6500QL
SERIES

Overmolded/Low-Profile Design

- Simplified cleaning and maintenance with fewer parts and crevices
- Advanced half facepiece design for a wide field of view
- Compatibility with welding/grinding shields

Silicone Face Seal

- Provides comfort and stability with a soft but firm face seal
- Extended product life due to resilient silicone material
- Our lightest silicone facepiece
 - Keeps its shape in high-heat environments



Cool Flow™ Valve

- Enhanced comfort by reducing heat and moisture
- Easier breathing with unique valve design



6500
SERIES

FULL LINE OF 3M™ HALF FACEPIECE REUSABLE RESPIRATORS

Depending on the types of environments you work in and the respirator qualities you favor, 3M is here to help you make the right choice for you.

6000 SERIES Half Facepiece Reusable Respirator		DEPENDABLE LIGHTWEIGHT VALUE	6500 SERIES Half Facepiece Reusable Respirator		RUGGED COMFORTABLE LOW PROFILE	7500 SERIES Half Facepiece Reusable Respirator		ADVANCED TECHNOLOGY ULTIMATE COMFORT
6100	Small		6501	Small		7501	Small	
6200	Medium		6502	Medium		7502	Medium	
6300	Large		6503	Large		7503	Large	
6100DD	Drop down, Small		6501QL	Quick Latch, Small				
6200DD	Drop down, Medium		6502QL	Quick Latch, Medium				
6300DD	Drop down, Large		6503QL	Quick Latch, Large				

For more information

Technical Service: 1-800-243-4630
Customer Service: 1-800-328-1667
3M.com/PPESafety

3M and Cool Flow are trademarks of 3M Company. Used under license in Canada. Please Recycle. Printed in the U.S.A. © 2013, 3M. All rights reserved.

70-0716-2625-6



WARNING

This respirator helps reduce exposures to certain airborne contaminants. Before use, the wearer must read and understand the User Instructions provided as a part of the product packaging. Follow all local regulations. In the U.S., a written respiratory protection program must be implemented meeting all the requirements of OSHA 1910.134, including training, fit testing and medical evaluation. In Canada, CSA standard Z94.4 requirements must be met and/or requirements of the applicable jurisdiction, as appropriate. Misuse may result in sickness or death. For proper use, see package instructions, supervisor, or call 3M PSD Technical Service in USA at 1-800-243-4630 and in Canada at 1-800-267-4414.



Personal Safety Division

3M Center, Building 235-2W-70
St. Paul, MN 55144-1000