

YES! ✓ WE CAN!



400 SERIES

Commercial KD Cabinets

FEATURES:

- All components precision engineered with no bolt heads showing on front and side panels.
- Body and shelves fabricated from 22 gauge steel.
- Shelves easily adjust up or down in 2" increments. Triple flanged shelf front for added strength (capacity up to 200 lbs).
- Reinforced doors swing a full 180°.
- Doors are factory-hung in 16 gauge frames ensuring proper performance.
- 16 gauge continuous hinges (72" high only).
- Corner foot gussets provide added rigidity and stability (replaced by mounting plates on mobile units).
- Mobile units include four heavy-duty locking swivel casters.
- Positive three-point locking (top, center and bottom) for secure locking (single cam only for 16" wide wall-mount cabinets).
- Plated locking handle has built-in cylinder key lock (keys included).

CONFIGURATIONS:

- Wall Mount
- Storage (includes 4 adjustable shelves)
- Wardrobe (includes 1 shelf and coat rod)
- Combination (includes 1 full width shelf, 3 half width shelves and a half width coat rod)

DOOR OPTIONS:

- Solid
- Safety-View (includes polycarbonate panels in door)
- Ventilated (includes expanded metal panels in door)



Wall Mount



STATIONARY STORAGE
Shown with
Solid Doors



MOBILE STORAGE
Shown with
Safety-View Doors



STATIONARY STORAGE
Shown with
Ventilated Doors

Description	Width	Depth	Height	Knock-Down Cat. No.			Assembled Cat. No.		
				Black	Gray	Parchment	Black	Gray	Parchment
SOLID DOOR CABINETS									
Wall Mount, Storage	16	12	26	34C173	34C222	34C125	34C197	34C246	34C149
Wall Mount, Storage	30	12	26	34C174	34C223	34C126	34C198	34C247	34C150
Wall Mount, Storage	36	12	30	34C175	34C224	34C127	34C199	34C248	34C151
Stationary, Storage	36	18	72	34C176	34C225	34C128	34C201	34C249	34C152
Stationary, Storage	36	24	72	34C177	34C226	34C129	34C202	34C250	34C153
Stationary, Storage	48	18	72	34C178	34C227	34C131	34C203	34C251	34C154
Stationary, Storage	48	24	72	34C179	34C228	34C132	34C204	34C252	34C155
Mobile, Storage	36	24	72	34C180	34C229	34C130	34C205	34C253	34C156
Mobile, Storage	48	24	72	34C181	34C230	34C133	34C206	34C254	34C157
SAFETY VIEW DOOR CABINETS									
Wall Mount, Storage	16	12	26	34C182	34C231	34C134	34C207	34C255	34C158
Wall Mount, Storage	30	12	26	34C183	34C232	34C135	34C208	34C256	34C159
Wall Mount, Storage	36	12	30	34C184	34C233	34C136	34C209	34C257	34C160
Stationary, Storage	36	18	72	34C185	34C234	34C137	34C210	34C258	34C161
Stationary, Storage	36	24	72	34C186	34C235	34C138	34C211	34C259	34C162
Stationary, Storage	48	18	72	34C187	34C236	34C140	34C212	34C260	34C163
Stationary, Storage	48	24	72	34C188	34C237	34C141	34C213	34C261	34C164
Mobile, Storage	36	24	72	34C189	34C238	34C139	34C214	34C262	34C165
Mobile, Storage	48	24	72	34C190	34C239	34C142	34C215	34C263	34C166
VENTILATED DOOR CABINETS									
Stationary, Storage	36	18	72	34C191	34C240	34C143	34C216	34C264	34C167
Stationary, Storage	36	24	72	34C192	34C241	34C144	34C217	34C265	34C168
Stationary, Storage	48	18	72	34C193	34C242	34C145	34C218	34C266	34C169
Stationary, Storage	48	24	72	34C194	34C243	34C146	34C219	34C267	34C170
Mobile, Storage	36	24	72	34C195	34C244	34C147	34C220	34C268	34C171
Mobile, Storage	48	24	72	34C196	34C245	34C148	34C221	34C269	34C172

COLOR SELECTION

708
 MIDNIGHT EBONY
(ME)

725
 HALLOWELL GRAY
(HG)

729
 PARCHMENT
(PT)