

## 300 IP TORX PLUS® Torque-indicator, pistol grip, 20 IP x 5.0 N m

### Series Torque-indicators



|                        |                |                               |              |
|------------------------|----------------|-------------------------------|--------------|
| <b>EAN:</b>            | 4013288099136  | <b>Size:</b>                  | 218x81x51 mm |
| <b>Part number:</b>    | 05028046001    | <b>Weight:</b>                | 220 g        |
| <b>Article number:</b> | 300 IP Pistole | <b>Country of origin:</b>     | CZ           |
|                        |                | <b>Customs tariff number:</b> | 82054000     |

- Torque-indicator with pre-set and tamperproof torque value
- Distinct audible and perceivable excess load signal when the pre-set torque value is reached
- Non-adjustable and tamperproof
- Unlimited torque for loosening seized screws
- Multi-component Kraftform pistol handle for fast and ergonomic screwdriving

Wera torque screwdriver with fixed torque for recessed TORX PLUS® screws. Tamperproof and with a slim hex blade. Unlimited torque for loosening seized screws. Multi-component Kraftform pistol handle for pleasant, ergonomic working that prevents blisters and calluses. Hard gripping zones for high working speeds whereas soft zones ensure high torque transfer.

#### Web link

[https://products.wera.de/en/torque\\_tools\\_series\\_torque-indicators\\_300\\_ip\\_pistole.html](https://products.wera.de/en/torque_tools_series_torque-indicators_300_ip_pistole.html)

Wera - 300 IP Pistole  
05028046001 - 4013288099136

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

### Torque-indicators



Wera torque-indicators have been factory pre-set to values recommended by leading carbide tool manufacturers. These tightening values relate specifically to the size of the TORX®, TORX PLUS® or hexagon socket screw. Torque indicators ensure safe and easy loosening of screw connections. Precision :  $\pm 10\%$

### Tamperproof




Non-adjustable and tamperproof.

### For difficult-to-access places



Slim 4 mm hexagon blades to reach screws in difficult-to-access places.

### Excess-load signal





Distinctly audible and noticeable excess-load signal when the pre-set torque is reached

### Pistol handle



Multi-component Kraftform pistol handle for fast and ergonomic screwdriving

### Further versions in this product family:

|             |  |     |        |  |  |  |  |  |  |
|-------------|-------------------------------------------------------------------------------------|-----|--------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|             |                                                                                     | Nm  | ft.lb. | mm                                                                                  | mm                                                                                  | mm                                                                                    | inch                                                                                  | mm                                                                                    | inch                                                                                  |
| 05028046001 | 20 IP                                                                               | 5.0 | 3.7    | 160                                                                                 | 100                                                                                 | 65                                                                                    | 2 9/16                                                                                | 25                                                                                    | 1                                                                                     |

### Web link

[https://products.wera.de/en/torque\\_tools\\_series\\_torque-indicators\\_300\\_ip\\_pistole.html](https://products.wera.de/en/torque_tools_series_torque-indicators_300_ip_pistole.html)

Wera - 300 IP Pistole

05028046001 - 4013288099136

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)