

Series 7400 Imperial Kraftform pre-set adjustable torque screwdrivers (2.5-29.0 in. lbs.) with Rapidaptor quick-release chuck, handle size 105 mm, art. no. 7466 x 11 in. lbs.

Series 7400 Kraftform Torque Screwdrivers, with a factory pre-set measurement value



<b>EAN:</b>	4013288103116	<b>Size:</b>	155x37x37 mm
<b>Part number:</b>	05074722001	<b>Weight:</b>	180 g
<b>Article number:</b>	7400 Imperial pre-set, 105 mm	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82054000



- Factory pre-set torque screwdriver with Rapidaptor quick-release chuck
- Only adjustable with an extra tool
- Suitable for bits with 1/4" hex head drive
- Rapidaptor technology for rapid bit change
- Distinct signal when pre-set value is reached

Wera torque screwdrivers. With a factory pre-set torque value set to the smallest scale value. For all applications, where the same constant torque and repeat accuracy are required. The torque can be changed with an extra tool within the measuring range (re-calibration kit can be ordered with the code number 05137001001). Afterwards you can check the set value using an off-the-shelf torque tester. Unlimited loosening torque for slackening stuck screws. Rapidaptor quick-release technology for rapid bit changes. Suitable for bits with a 1/4" external hexagon drive as per DIN ISO 1173-C 6.3 and E 6.3 (ISO 1173). Multi-component Kraftform handle with hard and soft zones for high working speeds, whilst being easy on the hand.

Please note: 1 Ncm = 0.01 Nm.

#### Web link

[https://products.wera.de/en/torque\\_tools\\_series\\_7400\\_kraftform\\_torque\\_screwdrivers\\_with\\_a\\_factory\\_pre-set\\_measurement\\_value\\_7400\\_imperial\\_pre-set\\_105\\_mm.html](https://products.wera.de/en/torque_tools_series_7400_kraftform_torque_screwdrivers_with_a_factory_pre-set_measurement_value_7400_imperial_pre-set_105_mm.html)

Wera - 7400 Imperial pre-set, 105 mm  
05074722001 - 4013288103116

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

Series 7400 Imperial Kraftform pre-set adjustable torque screwdrivers (2.5-29.0 in. lbs.) with Rapidaptor quick-release chuck, handle size 105 mm, art. no. 7466 x 11 in. lbs.

Series 7400 Kraftform Torque Screwdrivers, with a factory pre-set measurement value



#### Pre-set, adjustable torque screwdrivers



Wera torque screwdrivers. With a factory pre-set torque value set to the smallest scale value. For all applications, where the same constant torque and repeat accuracy are required. The torque can be changed with an extra tool within the measuring range (re-calibration kit can be ordered with the code number 05137001001). Afterwards you can check the set value using an off-the-shelf torque tester.

#### Unlimited torque



Unlimited torque for loosening seized screws.

#### Versatile



Rapidaptor technology makes the tool adaptable since bits and sockets can be exchanged rapidly.

#### Web link

[https://products.wera.de/en/torque\\_tools\\_series\\_7400\\_kraftform\\_torque\\_screwdrivers\\_with\\_a\\_factory\\_pre-set\\_measurement\\_value\\_7400\\_imperial\\_pre-set\\_\\_105\\_mm.html](https://products.wera.de/en/torque_tools_series_7400_kraftform_torque_screwdrivers_with_a_factory_pre-set_measurement_value_7400_imperial_pre-set__105_mm.html)

Wera - 7400 Imperial pre-set, 105 mm  
05074722001 - 4013288103116


Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

Series 7400 Imperial Kraftform pre-set adjustable torque screwdrivers (2.5-29.0 in. lbs.) with Rapidaptor quick-release chuck, handle size 105 mm, art. no. 7466 x 11 in. lbs.

Series 7400 Kraftform Torque Screwdrivers, with a factory pre-set measurement value



#### Chuck-all




The Rapidaptor quick-release chucks hold 1/4" DIN ISO 1173-C 6,3 and E 6,3 as well as Wera series 1 and 4 bits.

#### Rapid-in and self-lock



The bit can be pushed into the adaptor without moving the sleeve. The lock is activated automatically as soon as the bit is applied to the screw. Bits are held securely and wobble-free.

#### Rapid-out









Simply push the sleeve forward to change the bit. The spring mechanism lifts the bit off the magnet and unlocks the tool. The bit can be easily removed. The rapid-out function makes it easy to remove even the smallest bits without extra tools.

#### Kraftform



The basic idea for the prototype of the Kraftform handle – that the hand should dictate the design – has, right through to today, proved to be correct. In cooperation with the internationally recognised Fraunhofer IAO Institute, Wera developed a screwdriver handle designed to match the shape of the human hand as long ago as the 1960s. After a long development phase, the Wera Kraftform handle was launched to the market in 1968. It has been optimised through the years with new technologies, but has kept its proven shape. After all, the human hand has not changed either.

#### Further versions in this product family:

							
	art. no.	inch	in. lbs.	in. lbs.	mm	mm	inch
05074720001	7465	1/4	2.5	2.5-11.5	105	155	6
05074722001	7466	1/4	11.0	11.0-29.0	105	155	6

#### Web link

[https://products.wera.de/en/torque\\_tools\\_series\\_7400\\_kraftform\\_torque\\_screwdrivers\\_with\\_a\\_factory\\_pre-set\\_measurement\\_value\\_7400\\_imperial\\_pre-set\\_105\\_mm.html](https://products.wera.de/en/torque_tools_series_7400_kraftform_torque_screwdrivers_with_a_factory_pre-set_measurement_value_7400_imperial_pre-set_105_mm.html)

Wera - 7400 Imperial pre-set, 105 mm  
05074722001 - 4013288103116

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)