

# TRAFFIC CONES

Help safely manage traffic and more with the right traffic cones.




## KEY PRODUCT ATTRIBUTES

- Used for traffic management and safety purposes
- Designed with reflective bands for visibility
- Made with flexible, injection-molded PVC or polyethylene
- Ability to withstand high-speed impacts
- Can be doubled to increase weight
- Some bases can be filled with ballasts, or use sandbag rings for stability
- Stackable for easy storage
- Available in a variety of types, colors and sizes

## IN THE UNITED STATES, THEY COME IN SUCH SIZES AS:

- 12 in. (305mm), 1.5 lb. (0.68kg) – for indoor/outdoor applications
- 18 in. (457mm), 3 lb. (1.4kg) – for outdoor applications such as freeway line painting
- 28 in. (711mm), 7 lb. (3.2kg) – for non-highway applications e.g. local streets (also called Metro cones)
- 28 in. (711mm), 10 lb. (4.5kg) – for freeway/highway applications (with reflective stripes)
- 36 in. (914mm), 10 lb. (4.5kg) – for freeway/highway applications (with reflective stripes)



## PVC FLUORESCENT RED/ORANGE TRAFFIC CONES

### Meet MUTCD and NCHRP 350

Flexible, injection-molded PVC cones withstand high-speed impacts and snap back into shape. Stackable for easy storage.

Available in multiple styles:

Standard—Wide body, with matching color base.

Black Base—Wide body, with rugged black base.

Slim—Narrow, wind-resistant profile with orange base.

Recessed—Wide, 1-pc. body with orange base. Easier stacking with no pinch points for collars.

Note: May not be approved for highway projects in all states.

ITEM NO.	HEIGHT	DESCRIPTION	COLOR	BASE DIMENSION	WEIGHT
6FGY6	4"	Standard	Fluorescent Red/Orange	4"	0.11 lb.
6FGY7	6"	Standard	Fluorescent Red/Orange	6"	0.33 lb.
6FGY9	6"	Black Base	Fluorescent Red/Orange	6"	1.5 lb.
6FGY8	12"	Standard	Fluorescent Red/Orange	8"	2 lb.
6FGZ0	12"	Black Base	Fluorescent Red/Orange	8"	2 lb.
6FGZ7	18"	Standard	Fluorescent Red/Orange	10½"	2.3 lb.
6FHA0	18"	Standard	Fluorescent Red/Orange with Reflective Collars	11"	3 lb.
6FHA9	18"	Black Base	Fluorescent Red/Orange	11"	3 lb.
6FHC2	18"	Black Base	Fluorescent Red/Orange with Reflective Collars	11"	3 lb.
6FGZ1	18"	Slim	Fluorescent Red/Orange	11"	3 lb.
6FGZ4	18"	Slim	Fluorescent Red/Orange with Reflective Collars	11"	2.2 lb.
6FHC5	18"	Recessed	Fluorescent Red/Orange with Reflective Collars	11"	3 lb.
6FGZ8	28"	Standard	Fluorescent Red/Orange	14"	7 lb.
6FHA1	28"	Standard	Fluorescent Red/Orange with Reflective Collars	15"	7 lb.
6FHC0	28"	Black Base	Fluorescent Red/Orange	15"	7 lb.
6FHC3	28"	Black Base	Fluorescent Red/Orange with Reflective Collars	15"	7 lb.
6FGZ2	28"	Slim	Fluorescent Red/Orange	15"	5 lb.
6FGZ5	28"	Slim	Fluorescent Red/Orange with Reflective Collars	15"	5 lb.
6FHC6	28"	Recessed	Fluorescent Red/Orange with Reflective Collars	15"	7 lb.
6FGZ9	36"	Standard	Fluorescent Red/Orange	14"	10 lb.
6FHA2	36"	Standard	Fluorescent Red/Orange with Reflective Collars	14"	10 lb.
6FHC1	36"	Black Base	Fluorescent Red/Orange	14"	12 lb.
6FHC4	36"	Black Base	Fluorescent Red/Orange with Reflective Collars	14¾"	12 lb.
6FGZ3	36"	Slim	Fluorescent Red/Orange	13"	10 lb.
6FGZ6	36"	Slim	Fluorescent Red/Orange with Reflective Collars	14"	10 lb.
6FHC7	36"	Recessed	Fluorescent Red/Orange with Reflective Collars	14"	12 lb.





## PVC HEAVYWEIGHT FLUORESCENT RED/ORANGE TRAFFIC CONES

### Meet MUTCD and NCHRP 350

Flexible, injection-molded PVC cones withstand high-speed impacts and snap back into shape. Stackable for easy storage.

Available in multiple styles:

Standard—Wide body, with matching color base.

Slim—Narrow, wind-resistant profile with matching color base.



ITEM NO.	HEIGHT	DESCRIPTION	COLOR	BASE DIMENSION	WEIGHT
6TVF1	28"	Standard	Fluorescent Red/Orange	14 $\frac{3}{8}$ "	10 lb.
6VKG9	28"	Standard	Fluorescent Red/Orange with Reflective Collars	14 $\frac{3}{8}$ "	10 lb.
6VKH0	28"	Slim	Fluorescent Red/Orange	15"	10 lb.
6VKH1	28"	Slim	Fluorescent Red/Orange with Reflective Collars	15"	10 lb.


## PVC FLUORESCENT LIME GREEN TRAFFIC CONES

### Meet MUTCD and NCHRP 350

Flexible, injection-molded PVC cones withstand high-speed impacts and snap back into shape. Stackable for easy storage. Lime color differentiates a work zone from an emergency zone.

Available style:

Standard—Wide body, with matching color base.



ITEM NO.	HEIGHT	DESCRIPTION	COLOR	BASE DIMENSION	WEIGHT
6FHA3	18"	Standard	Fluorescent Lime	11"	2.2 lb.
6FHA6	18"	Standard	Fluorescent Lime with Reflective Collars	11"	2.2 lb.
6FHA4	28"	Standard	Fluorescent Lime	15"	7 lb.
6FHA7	28"	Standard	Fluorescent Lime with Reflective Collars	15"	7 lb.
6FHA5	36"	Standard	Fluorescent Lime	14"	10 lb.
6FHA8	36"	Standard	Fluorescent Lime with Reflective Collars	14"	10 lb.

## POLYETHYLENE COLORED TRAFFIC CONES

Injection-molded polyethylene cones are stackable for easy storage.

Available style:

Standard—Wide body, with matching color base.



ITEM NO.	HEIGHT	DESCRIPTION	►CHOOSE: COLOR	BASE DIMENSION	WEIGHT
H1545	18"	Standard	Blue, Green, Red, White, Yellow	11 x 11"	1.5 lb.