

YES! ✓ WE CAN!



800 SERIES Industrial KD Cabinets

FEATURES:

- All components precision engineered with no bolt heads showing on front and side panels.
- 20 gauge body and 22 gauge shelves provide strength and durability.
- Shelves easily adjust up or down in 2" increments. Triple flanged shelf front for added strength (capacity up to 250 lbs).
- Reinforced doors swing a full 180°.
- Doors are factory-hung in 16 gauge frames ensuring proper performance.
- 16 gauge continuous hinges.
- Corner foot gussets provide added rigidity and stability (replaced by mounting plates on mobile units).
- Mobile units include four heavy-duty locking swivel casters.
- Positive three-point locking (top, center and bottom) for secure locking.
- Plated locking handle has built-in cylinder key lock (keys included).

CONFIGURATIONS:

- Storage (includes 4 adjustable shelves)
- Wardrobe (includes 1 shelf and coat rod)
- Combination (includes 1 full width shelf, 3 half width shelves and a half width coat rod)

DOOR OPTIONS:

- Solid
- Safety-View (includes polycarbonate panels in door)
- Ventilated (includes expanded metal panels in door)



STATIONARY STORAGE
Shown with
Solid Doors



MOBILE STORAGE
Shown with
Ventilated Doors



STATIONARY WARDROBE
Shown with
Ventilated Doors



STATIONARY COMBINATION
Shown with
Safety-View Doors

Provides maximum protection to tools, dies, delicate instruments, supplies, and personal belongings. Neat and attractive in appearance. Designed to meet government requirements.

Description	Width	Depth	Height	Knock-Down Cat. No.		Assembled Cat. No.	
				Black	Parchment	Black	Parchment
SOLID DOOR CABINETS							
Stationary, Storage	36	18	78	6MNX6	6MNX0	6MNZ4	6MNY8
Stationary, Storage	36	24	78	6MNX7	6MNX1	6MNZ5	6MNY9
Stationary, Storage	48	18	78	34A363	34A290	34A399	34A327
Stationary, Storage	48	24	78	34A366	34A293	34A403	34A330
Stationary, Wardrobe	36	18	78	6MNX8	6MNX2	6MNZ6	6MNZ0
Stationary, Wardrobe	36	24	78	6MNX9	6MNX3	6MNZ7	6MNZ1
Stationary, Wardrobe	48	18	78	34A372	34A299	34A409	34A336
Stationary, Wardrobe	48	24	78	34A375	34A303	34A412	34A339
Stationary, Combination	36	18	78	6MNY0	6MNX4	6MNZ8	6MNZ2
Stationary, Combination	36	24	78	6MNY1	6MNX5	6MNZ9	6MNZ3
Stationary, Combination	48	18	78	34A378	34A306	34A415	34A342
Stationary, Combination	48	24	78	34A381	34A309	34A418	34A345
Mobile, Storage	36	24	78	34A352	34A279	34A388	34A316
Mobile, Storage	48	24	78	34A369	34A296	34A406	34A333
SAFETY VIEW DOOR CABINETS							
Stationary, Storage	36	18	78	34A348	34A275	34A384	34A312
Stationary, Storage	36	24	78	34A350	34A277	34A386	34A314
Stationary, Storage	48	18	78	34A364	34A291	34A401	34A328
Stationary, Storage	48	24	78	34A367	34A294	34A404	34A331
Stationary, Wardrobe	36	18	78	34A355	34A282	34A391	34A319
Stationary, Wardrobe	36	24	78	34A357	34A284	34A393	34A321
Stationary, Wardrobe	48	18	78	34A373	34A301	34A410	34A337
Stationary, Wardrobe	48	24	78	34A376	34A304	34A413	34A340
Stationary, Combination	36	18	78	34A359	34A286	34A395	34A323
Stationary, Combination	36	24	78	34A361	34A288	34A397	34A325
Stationary, Combination	48	18	78	34A379	34A307	34A416	34A343
Stationary, Combination	48	24	78	34A382	34A310	34A419	34A346
Mobile, Storage	36	24	78	34A353	34A280	34A389	34A317
Mobile, Storage	48	24	78	34A370	34A297	34A407	34A334
VENTILATED DOOR CABINETS							
Stationary, Storage	36	18	78	34A349	34A276	34A385	34A313
Stationary, Storage	36	24	78	34A351	34A278	34A387	34A315
Stationary, Storage	48	18	78	34A365	34A292	34A402	34A329
Stationary, Storage	48	24	78	34A368	34A295	34A405	34A332
Stationary, Wardrobe	36	18	78	34A356	34A283	34A392	34A320
Stationary, Wardrobe	36	24	78	34A358	34A285	34A394	34A322
Stationary, Wardrobe	48	18	78	34A374	34A302	34A411	34A338
Stationary, Wardrobe	48	24	78	34A377	34A305	34A414	34A341
Stationary, Combination	36	18	78	34A360	34A287	34A396	34A324
Stationary, Combination	36	24	78	34A362	34A289	34A398	34A326
Stationary, Combination	48	18	78	34A380	34A308	34A417	34A344
Stationary, Combination	48	24	78	34A383	34A311	34A420	34A347
Mobile, Storage	36	24	78	34A354	34A281	34A390	34A318
Mobile, Storage	48	24	78	34A371	34A298	34A408	34A335

