

## 300 IP TORX PLUS® Torque-indicator, 8 IP x 1.2 N m

### Series Torque-indicators



|                        |               |                               |              |
|------------------------|---------------|-------------------------------|--------------|
| <b>EAN:</b>            | 4013288093431 | <b>Size:</b>                  | 170x37x37 mm |
| <b>Part number:</b>    | 05028042001   | <b>Weight:</b>                | 116 g        |
| <b>Article number:</b> | 300 IP        | <b>Country of origin:</b>     | CZ           |
|                        |               | <b>Customs tariff number:</b> | 82054000     |

- Torque-indicator with pre-set and tamperproof torque value
- Distinct audible and perceivable excess load signal when the pre-set torque value is reached
- Non-adjustable and tamperproof
- Unlimited torque for loosening seized screws
- Multi-component Kraftform handle for fast and ergonomic screwdriving

Wera torque screwdriver with fixed torque for recessed TORX PLUS® screws. Tamperproof and with a slim hex blade. Unlimited torque for loosening seized screws. Multi-component Kraftform handle for pleasant, ergonomic working that prevents blisters and calluses. Hard gripping zones for high working speeds whereas soft zones ensure high torque transfer.

#### Web link


[https://products.wera.de/en/torque\\_tools\\_series\\_torque-indicators\\_300\\_ip.html](https://products.wera.de/en/torque_tools_series_torque-indicators_300_ip.html)

Wera - 300 IP

05028042001 - 4013288093431


Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

### Torque-indicators



Wera torque-indicators have been factory pre-set to values recommended by leading carbide tool manufacturers. These tightening values relate specifically to the size of the TORX®, TORX PLUS® or hexagon socket screw. Torque indicators ensure safe and easy loosening of screw connections. Precision :  $\pm 10\%$

### For difficult-to-access places



Slim 4 mm hexagon blades to reach screws in difficult-to-access places.

### Tamperproof



Non-adjustable and tamperproof.

### Excess-load signal




Distinctly audible and noticeable excess-load signal when the pre-set torque is reached

### Kraftform



The basic idea for the prototype of the Kraftform handle – that the hand should dictate the design – has, right through to today, proved to be correct. In cooperation with the internationally recognised Fraunhofer IAO Institute, Wera developed a screwdriver handle designed to match the shape of the human hand as long ago as the 1960s. After a long development phase, the Wera Kraftform handle was launched to the market in 1968. It has been optimised through the years with new technologies, but has kept its proven shape. After all, the human hand has not changed either.

### Kraftform handle



Multi-component Kraftform handle with hard and soft zones for fast working speeds and protecting the palm of the hand.

### Web link

[https://products.wera.de/en/torque\\_tools\\_series\\_torque-indicators\\_300\\_ip.html](https://products.wera.de/en/torque_tools_series_torque-indicators_300_ip.html)

Wera - 300 IP

05028042001 - 4013288093431

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)

Further versions in this product family:

|                    |  |            |            |  |  |  |  |  |
|--------------------|---|------------|------------|---|--|---|---|---|
|                    |   | Nm         | ft. lb.    | mm  | mm   | mm  | mm  | inch  |
| 05028040001        | 6 IP  | 0.6        | 0.4        | 4   | 3.5  | 65  | 105   | 2 9/16  |
| 05028041001        | 7 IP  | 0.9        | 0.7        | 4   | 3.5  | 65  | 105   | 2 9/16  |
| <b>05028042001</b> | <b>8 IP</b>   | <b>1.2</b> | <b>0.9</b> | <b>4</b>  | <b>3.5</b>   | <b>65</b>   | <b>105</b>  | <b>2 9/16</b>   |
| 05028043001        | 9 IP  | 1.4        | 1.0        | 4   | 3.5  | 65  | 105   | 2 9/16  |
| 05028044001        | 10 IP   | 2.0        | 1.5        | 4   | 3.8  | 65  | 105   | 2 9/16  |
| 05028045001        | 15 IP   | 3.0        | 2.2        | 4   | 3.8  | 65  | 105   | 2 9/16  |

## Web link

[https://products.wera.de/en/torque\\_tools\\_series\\_torque-indicators\\_300\\_ip.html](https://products.wera.de/en/torque_tools_series_torque-indicators_300_ip.html)

Wera - 300 IP

05028042001 - 4013288093431

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)