

Exceptional fit and feel for extended wear

- Thick design for durable protection
- Fully textured for enhanced grip



Industries

- Food Processing
- Life Sciences
- Healthcare

Recommended For

- Equipment, maintenance and repair
- All food processing, applications that have food contact
- Sample taking and processing
- Extra comfort during long, sustained procedures
- Standard patient examinations



TECHNICAL DATA SHEET

PRODUCT INFORMATION

	Diamond Grip Plus® DGP-350
Material	Natural Rubber Latex
Color	Natural
Glove Design	Chlorinated, Powder-Free, Silicone Free, Fully Textured
Cuff	Beaded
Manufacturing/QMS Audit Standards	EN ISO 13485:2012
Regulatory/Standards Compliance	ASTM D3578, EN 420:2003 + A1:2009, FDA21 CFR 177-2600, US QSR/FDA 510(k) Medical Examination Grade
Packaging	100 gloves per dispenser 10 dispensers per case 1000 gloves per case
Storage	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country of Origin	Malaysia
Available sizes	XS (5.5 - 6), S (6.5 - 7), M (7.5 - 8), L (8.5 - 9), XL (9.5 - 10)
Anti-static	Not Tested

PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	245 / 9.6		ASTM D3767,EN 420
Freedom from Holes (Inspection level I)	1.5 AQL		ASTM D5151,EN 455-1
Palm Thickness (mm/mils)	0.13 / 5.1		ASTM D3767,EN 420
Finger Thickness (mm/mils)	0.16 / 6.3		ASTM D3767,EN 420
	BEFORE AGING	AFTER AGING	
Ultimate Tensile Strength (MPa)	22	20	ASTM D412 & D573
Elongation at Break (%)	≥ 700	≥ 600	ASTM D412
Force at break (N)	9	9	EN 455-2

ORDERING INFORMATION

Size	XS (5.5 - 6)	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)
Product Code	DGP-350-XS	DGP-350-S	DGP-350-M	DGP-350-L	DGP-350-XL

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
T: +603 8310 6688
F: +603 8310 6699

North America Region

Ansell Healthcare Products LLC
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Australia

Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

Russia

Ansell PYC
Ten. +7 495 258 13 16

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.