

## WHOLE HOUSE FAN CEILING SHUTTERS

### HVAC/R fact sheet

#### ECONOMY-LOW VELOCITY

This model is a low velocity exhaust ceiling shutter. The flanged frame and blades are aluminum with a Polar White finish. The blades have a felt seal on the leading edge for quiet closing. The shutter utilizes tie rods on both ends of the blades for uniform opening when the fan is operating. Ideal for use with whole house fans. Recommended for horizontal mount exhaust in residential ceilings.

Sizes available – 16" W x 16" H to 38" W x 38" H.  
Maximum free area velocity – 1500 FPM.



3HHR4

#### PREMIUM CEILING SHUTTER

This model is our premium exhaust ceiling shutter. The flanged frame and blades are aluminum with a Polar White finish. The blades have a galvanized reinforcement strip across the top of each blade for added strength and counter balancing efficiency. The blades have a felt seal on the leading edge for quiet closing. The shutter utilizes tie rods on both ends of the blades for uniform opening when the fan is operating. Ideal for use with whole house fans. Recommended for horizontal mount exhaust in residential ceilings.

Sizes available – 16" W x 16" H to 50" W x 50" H.  
Maximum free area velocity – 2250 FPM.



4C225

#### CEILING TRUSS SHUTTER

This model is an exhaust ceiling shutter that installs without framing or cutting the ceiling joist. The flanged frame and blades are aluminum with a Polar White finish. The blades have a felt seal on the leading edge for quiet closing. The shutter utilizes tie rods on both ends of the blades for uniform opening when the fan is operating. Ideal for use with whole house fans. Recommended for horizontal mount exhaust in residential ceilings.



3C510

FITS FAN DIA. (IN.)	L (In.)	W (In.)	OPENING REQ. (In.)	ITEM NO.
<b>ECONOMY CEILING TRUSS SHUTTERS</b>				
24	26	32	24L x 30W	<b>3C510</b>
24	30 3/4	29 11/16	28 3/4L x 27 11/16W	<b>4HA10</b>
30	30 3/4	35 7/8	28 3/4L x 33 7/8W	<b>4HA11</b>
30	32	32	30L x 30W	<b>3C511</b>
36	36	32	34L x 30W	<b>3C512</b>
36	37 3/4	36	35 3/4L x 34W	<b>4HA12</b>
<b>ECONOMY CEILING SHUTTERS</b>				
24	26	26	24L x 24W	<b>3HHR2</b>
30	32	32	30L x 30W	<b>3HHR3</b>
36	36	36	34L x 34W	<b>3HHR4</b>
<b>PREMIUM CEILING TRUSS SHUTTERS</b>				
24	32	26	30L x 24W	<b>3HHR6</b>
30	35	32	33L x 30W	<b>3HHR7</b>
42	42	40	40L x 38W	<b>3HHR8</b>
42	43	32	41L x 30W	<b>3HHR9</b>
<b>PREMIUM CEILING SHUTTERS</b>				
24	26	26	24L x 24W	<b>4C224</b>
30	32	32	30L x 30W	<b>4C225</b>
36	35	40	33L x 38W	<b>3HHR5</b>
36	38	38	36L x 36W	<b>4C228</b>
42	44	44	42L x 42W	<b>3C242</b>
48	50	50	48L x 48W	<b>3C243</b>

Find it at Grainger.

Call or visit your local branch or go to [grainger.com/dayton](http://grainger.com/dayton) for complete product line information.