



MAKE YOUR MARK

## LONG TAPE MEASURES

### MC SERIES

The MC Series long tapes feature a compact, closed metal case that fits nicely in your hand and protects the tape. Blades are heavy-duty, with 40,000 strands of fiberglass to ensure a long life. Tape is stretch resistant and extremely resilient and metal crank handle provides years of rugged use. Double throat rollers guide the blade return and prevents the tape from twisting.



MC18100

Limited lifetime warranty.

| MODEL     | UPC<br>(052837) | LENGTH      | UNITS                         | ZERO PT. | ATTACHMENT  | BLADE    |
|-----------|-----------------|-------------|-------------------------------|----------|-------------|----------|
| MC1850    | 000104          | 50 ft.      | ft, in, 1/8                   | Hook End | Hook        | F1       |
| MC1050    | 001309          | 50 ft.      | ft, 1/10, 1/10                | Hook End | Hook        | F2       |
| MC181050  | 000708          | 50 ft.      | ft, in, 1/8 & ft, 1/10, 1/100 | Hook End | Double Hook | F1 & F14 |
| MC18M50   | 000401          | 50 ft./15m  | ft, in, 1/8 & m, cm, 2mm      | Hook End | Double Hook | F1 & F13 |
| MC10M50   | 001002          | 50 ft./15m  | FT, 1/10, 1/100 & m, cm, 2mm  | Hook End | Double Hook | F2 & F13 |
| MC18100   | 000111          | 100 ft.     | ft, in, 1/8                   | Hook End | Hook        | F1       |
| MC10100   | 001316          | 100 ft.     | ft, 1/10, 1/10                | Hook End | Hook        | F2       |
| MC1810100 | 000715          | 100 ft.     | ft, in, 1/8 & ft, 1/10, 1/100 | Hook End | Double Hook | F1 & F14 |
| MC18M100  | 000418          | 100 ft./30m | ft, in, 1/8 & m, cm, 2mm      | Hook End | Double Hook | F1 & F13 |
| MC10M100  | 001019          | 100 ft./30m | FT, 1/10, 1/100 & m, cm, 2mm  | Hook End | Double Hook | F2 & F13 |
| MC18165   | 000128          | 165 ft.     | ft, in, 1/8                   | Hook End | Hook        | F1       |

### AVAILABLE IN

**F = 1/2-inch wide, fiberglass, long tape**



F1 = Hook, Zero = Hook end, SAE ft., in., 1/8



F2 = Hook, Zero = Hook end, ENG: ft., 1/10, 1/100



F13 = Hook, Zero = Hook end, Metric (YELLOW): cm, mm



F14 = Hook, Zero = Hook end, ENG (YELLOW): ft., 1/10, 1/100

MC Series Long Tape Sell Sheet