


MEGAPRO⁺

Every bit better.

**PROFESSIONAL
MULTI-BIT SCREWDRIVERS**

MEGAPRO SCREWDRIVER PATENTED FEATURES



EZ-Guide™ Collar

- Provides greater control
- Maintains alignment between the screwdriver and the fastener
- Essential when starting to drive a screw

Retractable Bit Cartridge™

- Cartridge pulls out from inside the Megapro Screwdrivers Handle
- Convenient storage area with built in clips for seven double ended bits
- Allows for easy selection and quick change of required bits

Palm Saver Cap™

- Cap stays stationary while turning the handle
- Allows for one-handed use of the screwdriver
- Largest cap surface in the industry for hand tools, does not blister the palm of your hand

ABOUT MEGAPRO⁺ SCREWDRIVERS

Megapro Screwdrivers have been made in South Bend, IN since 1994

All Megapro screwdrivers are backed by a lifetime warranty for manufacturer defects

Since 1994 Megapro has sold over 4 million screwdrivers and has not had a single handle or shaft break













MEGAPRO[®]

DRIVERS

MEGAPRO PART#

GRAINGER
SKU#

DESCRIPTION

 <p>0+3 1+2 0+3 1+2 10+15 20+25 4+6</p>	<p>151NAS-B</p>	<p>5PA32</p>	<p>15in 1 Original driver with a bit-load that includes: Phillips (0,1,2,3) Robertson (0,1,2,3) Flat (4,6) TORX (10,15,20,25)</p>
 <p>SECURITY BITS 1/8+9/64 5/32+3/16 6+8 10+12 10+15 20+25 27+30</p>	<p>151TP-B</p>	<p>5PA34</p>	<p>15in 1 Tamperproof driver with a bit-load that includes: Hex-pin (1/8, 9/64, 5/32, 3/16) Spanner (6,8,10,12) TORX-pin (10,15,20,25,27,30)</p>
 <p>SECURITY BITS Tri-Wing 2+3 4+5 Torq-Set 4+6 8+10 Torx-Plus TR 10+15 20+25 27+30</p>	<p>151TP2-B</p>	<p>2MRR8</p>	<p>15in 1 Tamperproof 2 driver with a bit-load that includes: Tri-wing (2,3,4,5) TORX-set (4,6,8,10) TORX-plus tamper resistant (10,15,20,25,27,30)</p>
 <p>Standard 3/32+7/64 1/8+9/64 5/32+3/16 7/32+1/4 Metric (mm) 2+3 4+5 5.5+6</p>	<p>151HX-B</p>	<p>1PMA8</p>	<p>15in 1 Hex (Allen) driver with a bit-load that includes: Standard Hex tips (3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4) Metric tips (2,3,4,5,5.5,6)</p>
 <p>Made in Canada Patented ZAD 8 Zinc Alloy SOLID-CORE ratchet with 28 teeth for smoother use</p> <p>0+3 1+2 1+2 10+15 20+25 4+6</p>	<p>211R2C36RD-B</p>	<p>4KTF9</p>	<p>13in1 Ratcheting driver with a bit-load that includes: Phillips (0,1,2,3) Robertson (1,2) Flat (4,6) TORX (10, 15, 20, 25)</p>
 <p>Square Awl for puncturing sheet metal Phillips 0+3 1+2 2+2 Square Awl 3+5 5.5 Slot 4+6 VST</p>	<p>141HVAC-U-B</p>	<p>4KTG1</p>	<p>14in 1 HVAC driver with a bit-load that includes: Phillips (0,1,2,3) Square Awl, Valve stem bit, Double-Lock Phillips #2 Flat (3,5,5.5,4,6)</p>
 <p>Features a 1/4" quick-change chuck that locks the bit into the driver and accepts all hex shank power groove accessories.</p> <p>0+3 1+2 0+3 1+2 10+15 20+25 4+6</p>	<p>181ML-B</p>	<p>5PA35</p>	<p>15in 1 MegaLok driver with a bit-load that includes: Phillips (0,1,2,3) Robertson (0,1,2,3,) Flat (4,6) TORX (10,15,20,25) Double-Lok bits</p>
 <p>Features a stainless steel shaft and electroless nickel plated bits (rust resistant)</p> <p>0+3 1+2 0+3 1+2 10+15 20+25 4+6</p>	<p>151SS-B</p>	<p>5PA33</p>	<p>15in 1 Stainless Steel driver with a bit-load that includes: Phillips (0,1,2,3) Robertson (0,1,2,3,) Flat (4,6) TORX (10,15,20,25)</p>
 <p>Features lock mechanism that locks the bits into the shaft until released by the user</p> <p>0+3 1+2 0+3 1+2 10+15 20+25 4+6</p>	<p>151SL44-B</p>	<p>2FRU2</p>	<p>15in 1 ShaftLok driver with a bit-load that includes: Phillips (0,1,2,3) Robertson (0,1,2,3,) Flat (4,6) TORX (10,15,20,25)</p>
 <p>Features a mix of Tamperproof and standard bits for elevator service technicians</p> <p>Phillips 0+3 1+2 Spanner 6+8 10+12 Torx Pin 10+15 20+25 Slot 4+6</p>	<p>151ELEV-CH/OR-B</p>	<p>4KTG2</p>	<p>15in 1 Elevator driver with a bit-load that includes: Phillips (0,1,2,3) Spanner(6,8,10,12) Flat (4,6) TORX-pin (10,15,20,25)</p>





















MEGAPRO[®]

DRIVERS

MEGAPRO PART#





GRAINGER
SKU#

DESCRIPTION

 <p>1/4" Socket Adapter</p> 	<p>141AUTO-B</p>	<p>35HV08</p>	<p>14in 1 Automotive driver with a bit-load that includes: Phillips (1,2) Flat (5.5) ValveStem Bit, 1/4" Socket Adapter, TORX (9,10,15,20,25,27,30,40)</p>
 	<p>151JOBSITE-B</p>	<p>22XT28</p>	<p>15in 1 JOBSITE driver with a bit-load that includes: Phillips (0,1,2,3) Hex (1/8, 9/64, 5/32, 3/16) Flat (4,6) TORX (10,15,20,25)</p>
 <p>Features a round awl useful for untying knots</p> 	<p>151OUTDOOR-B</p>	<p>22XT29</p>	<p>15in 1 OUTDOORS driver with a bit-load that includes: Phillips (0,1,2,3) Robertson (1,2) Flat (4,6) TORX (10,15,20,25) Round Awl Reamer</p>
<p>Canada Made in Canada</p>  <p>SECURITY BITS</p> 	<p>211R2CTPRD-B</p>	<p>22XT27</p>	<p>13in 1 Tamperproof Ratcheting driver with a bit-load that includes: Hex-pin (1/8, 9/64) Spanner (6,8,10,12) TORX-pin (10,15,20,25,27,30)</p>
<p>Canada Made in Canada</p>  <p>SECURITY BITS</p> 	<p>211CG2CTP-B</p>	<p>22XT30</p>	<p>13in1 Tamperproof True Grip driver with a bit-load that includes: Hex-pin (1/8, 9/64) Spanner (6,8,10,12) TORX-pin (10,15,20,25,27,30)</p>
<p>Canada Made in Canada</p>  <p>Features a rubberized cushion grip for superior comfort and ease of use</p> 	<p>211CG2CNAS-B</p>	<p>22XT31</p>	<p>13in1 True Grip driver with a bit-load that includes: Phillips (0,1,2,3) Robertson (1,2) Flat (4,6) TORX (10, 15, 20, 25)</p>
<p>\$1.00 from every Pink Driver sold goes to support breastcancer.org</p>  	<p>151PK/WH-B</p>	<p>35HV04</p>	<p>15in 1 Pink driver with a bit-load that includes: Phillips (0,1,2,3) Robertson (0,1,2,3) Flat (4,6) TORX (10,15,20,25)</p>
<p>Fixed Shaft</p>  <p>Canada Made in Canada</p> 	<p>211R2T36STD-B</p>	<p>35HV05</p>	<p>13in1 Standard T-Handle driver with a bit-load that includes: Phillips (0,1,2,3) Robertson (1,2) Flat (4,6) TORX (10, 15, 20, 25)</p>
<p>Features a robust design to provide extra torque for serious industrial use</p>  <p>Ratcheting</p>  <p>Canada Made in Canada</p>	<p>211R2T36RD-B</p>	<p>35HV06</p>	<p>13in1 Ratcheting T-Handle driver with a bit-load that includes: Phillips (0,1,2,3) Robertson (1,2) Flat (4,6) TORX (10, 15, 20, 25)</p>
<p>Features four tips for precision fastening</p>  	<p>6PDRIVER-CC-B</p>	<p>35HV09</p>	<p>4in 1 Pocket driver with a bit-load that includes: Phillips (00,0) Flat (1.5,2)</p>

MEGAPRO[®]

ACCESSORIES AND BITS

	MEGAPRO PART#	GRAINGER SKU#	DESCRIPTION
SLIM PROFILE LOCKING EXTENSIONS  6" SHAFTLOK Extension  10" SHAFTLOK Extension	6EXT-SL6-B	2MRT8	Precision machined from a single steel rod, both 6" and 10" extensions are exclusive to the ShaftLok driver, Combine multiple extensions for greater reach
	6EXT-SL10-B	2MRT9	
 	6MEGALITE-C-B	4KTG3	Small battery powered LED Megalite clips onto the shaft of most Megapro drivers. Allows for illuminated screw driving. Batteries also included

FULL RANGE OF REPLACEMENT BIT PACKS

All replacement bits are made from professional quality S2 steel for the right combination of strength and durability. The Electroless Nickel Plated (ENP) bits provide outstanding protection against rust and corrosion. DoubleLok bits can also be used in corded and cordless drills. Only ShaftLok bits fit into the ShaftLok driver.



MEGAPRO PART#	GRAINGER SKU#	DESCRIPTION
9BP-ENPD-3A-B	5PA36	Includes: DoubleLok Phillips (1, 2) Flat (4, 6) and Robertson (1, 2)
9BP-ENPD-2A-B	5PA37	Includes: DoubleLok Phillips (0, 3) and Robertson (0, 3)
9BP-ENPD-2B-B	5PA38	Includes: DoubleLok TORX (10, 15) and TORX (20, 25)
9BP-TP-3A-B	5PA39	Includes: Spanner (6, 8) Spanner (10, 12) and TORX-pin (10, 15)
9BP-TP-2A-B	5PA40	Includes: TORX-pin (20, 25) and TORX-pin (27, 30)
9BP-TP-2B-B	5PA41	Includes: Hex-pin (1/8, 9/64) and Hex-pin (5/32, 3/16)
9BP-TP-1A-B	2MRR9	Includes: Spanner (14)
9BP-HX-3A-B	1TLJ4	Includes: Metric Hex (2, 3) Metric Hex (4, 5) and Metric Hex (5.5, 6)
9BP-HX-2A-B	1TLJ5	Includes: Hex (3/32, 7/64) and Hex (1/8, 9/64)
9BP-HX-2B-B	1TLJ6	Includes: Hex (5/32, 3/16) and Hex (7/32, 1/4)
9BP-AH-3A-B	1TLJ1	Includes: Socket Adaptor (1/4") TORX (9, 40) and Flat (5.5)/Valve Stem Bit
9BP-CG-2A-B	1TLJ2	Includes: Flat (2, 4) and Flat (3, 5)
9BP-CG-2B-B	1TLJ3	Includes: Hex Nut Driver (3/16) and Threaded Screw Starter (5.3 x 4.0 x 50)
9BP-SL-3A-B	2MRT1	Includes: ShaftLok Flat (4, 6) Phillips (1, 2) and Robertson (1, 2)
9BP-SL-2A-B	2MRT2	Includes: ShaftLok Phillips (0, 3) and Robertson (0, 3)
9BP-SL-2B-B	2MRT3	Includes: ShaftLok TORX (10, 15) and TORX (20, 25)

For more information contact your Grainger Representative or visit Grainger.com

AVAILABLE THROUGH

GRAINGER[®]

FOR THE ONES WHO GET IT DONE