

PIG® HazMat Spill Kit in 95-Gallon Overpack Salvage Drum

#KIT302 - Absorbs up to 63 gal. • No Wheels • UN1H2/X295/S



Strong enough to earn a UN rating for shipping chemical spill cleanup waste.

- Comply with Spill Plan regs, avoid fines and be ready to respond with the #1 kit for chemical spills
- Overpack drum container is UN Rated for shipping waste after spill cleanup
- Lift-out, prepacked baskets speed access and guard contents from UV
- PIG HazMat Socks stop spreading spills; PIG HazMat Pads and Pillows absorb quickly
- PIG HazMat Absorbents are specially treated for unsurpassed performance with concentrated corrosives, such as 98% sulfuric acid and 30% sodium hydroxide
- Overpack is X-rated in Packing Groups I, II and III for shipping spill cleanup waste by land, sea or rail
- Lightweight, 100% polyethylene container resists chemicals and keeps contents clean and dry
- Leakproof, twist-on lid is notched for easy removal or tightening with a 2x4 or pole
- Large, color-coded label makes identification fast and accurate
- Ledges molded into container make kit easy to move by forklift
- Tamperproof seals help prevent pilfering of spill response supplies
- Note: A PIG Overpack Protection Cover (available separately) is suggested for outdoor storage to protect container from UV degradatio
- Only PIG Spill Kits feature PIG HazMat Absorbents that handle highly concentrated corrosives better than any other absorbent on the market
- For information on custom spill kits, just call 1-800-HOT-HOGS (468-4647)

Always in stock. Ships within 24 hours.



By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

New Pig

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: KIT302 - Pg 1 of 2

KIT302 Specifications

Fluids Absorbed:	Acids, Bases & Unknowns
Absorbency:	Up to 63 gal.
Spill Volume:	50 - 79 gal.
Lift-out Basket:	Yes
Outdoor Storage:	Yes
UN Rated:	Yes
UV Resistant:	Yes
Wheels:	No
Sold as:	1 each
Weight:	100 lbs.
National Stock Number (NSN):	4235-01-416-9593
# per Pallet:	2
Composition:	Socks, Mats, Pillows & Dikes - Polypropylene Skin & Filler
Includes:	12 - ext. dia. 3" x 46" L PIG® HazMat Chemical Absorbent Sock (124CR) 6 - ext. dia. 3" x 10' L PIG® HazMat Chemical Absorbent Sock (PIG301) 2 - ext. dia. 5" x 10' L PIG® HazMat Chemical Absorbent Dike (HA1010) 7 - 17" W x 16" L x 2" H PIG® HazMat Chemical Absorbent Pillow (HR7015) 75 - 15" W x 20" L PIG® HazMat Mat Pad (MAT301) 10 - 36" W x 60" H Polyethylene Disposal Bags (BAG201-L) 6 - 2" W x 6" L Tamperproof Seal Label (LBL100) 1 - Instructions
UNSPSC:	47131905

KIT302 Metric Equivalent

Absorbency:	Up to 238.5 L
Weight:	45.4 kg

Technical Information

Warnings & Restrictions:

HAZ-MAT Notice
To ensure effectiveness and your safety, we recommend that you conduct compatibility and absorption testing of your chemicals with PIG® HAZ-MAT products prior to purchase. If you have any questions or need samples to test, please call Technical Services.
This product can ONLY be shipped to the United States or Canada.

Certifications, Approvals and Ratings:

UN1H2/X295/S

Regulations and Compliance:

49 CFR 173.3(c)(1) - If a container of hazardous waste is damaged or leaking, it can be placed in a compatible salvage drum that meets UN criteria for shipping.

29 CFR 1910.120(j)(1)(vii) - OSHA's HAZWOPER standard requires spill responders to have, "DOT specified salvage drums or containers and suitable quantities of proper absorbents," in areas where spills may occur.

Technical Documents:

(Available at newpig.com)

Product Data Sheet (PDS)

Safety Data Sheet (SDS)

Chemical Compatibility (CCG)



New Pig

By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: KIT302 - Pg 2 of 2