

FTP SERIES

FIBERGLASS TRIPOD STEPLADDER

Fully braced front section

Convenient spreader handle design improves setup and transportability

Model shown
FTP6206

Fiberglass Tripod StepLadder
FTP6200 Series



300 lbs.

LOAD CAPACITY
Combined Weight of User and Materials

Type IA Duty Rating

Double riveted comfortable Traction-Tred® steps for slip-resistance and durability

Molded external rail shield helps protect against abrasion and rail damage




Tool-Tra-Top® with drill holster, tools and paint can holder



Extra clear-width for comfortable climbing; lower spreader location for open work area



Wear resistant aluminum outrigger protects rail connections



Replaceable riveted, slip-resistant foot pad






Heavy Duty Fiberglass Tripod Stepladder

- Tool-Tra-Top® with drill holster/paint can holder
- Extra clear-width for comfortable climbing
- Fully braced front section
- Easy close & carry spreaders
- Double riveted comfortable Traction-Tred® steps for slip-resistance and durability
- Wear resistant aluminum outrigger protects rail connections
- Replaceable riveted, slip-resistant foot pad
- Molded external rail shield helps protect against abrasion and rail damage

Tripod Ladder FTP6200 Series

★★★★★
300 lbs.
LOAD CAPACITY
Combined Weight of User and Materials
Type IA Duty Rating



Model shown
FTP6206

SPECIFICATIONS FTP6200 Series

Model No.	Size	Approx. Width	Approx. Spread	Cu. Ft. Per Unit	Approx. Ship Wt. Lbs.	Approx. Load Capacity†
FTP6204	4'	31"	30"	3.7	17	300 lbs.
FTP6206	6'	36"	30"	9.9	23	300 lbs.
FTP6208	8'	40"	30"	10.1	31	300 lbs.
FTP6210	10'	51"	30"	17.6	42	300 lbs.
FTP6212	12'	54"	30"	22.6	51	300 lbs.

† Load capacity combines the total weight of both the user and the materials.

DIMENSIONS

Top:	5-3/4" x 13"	Steps:	3" wide
Front Rails:	3-1/8" wide	Rear Rails:	1-1/2" square (4' to 8')
Flange:	1-3/16" wide		2" square (10' and 12')

Universal Product Code

Model No.	UPC
FTP6204	0 51751 06470 4
FTP6206	0 51751 06471 1
FTP6208	0 51751 06472 8
FTP6210	0 51751 06473 5
FTP6212	0 51751 06474 2



GM6485 ©2003 Werner Co. Printed in U.S.A. July 2003