

marathon

America's Flat Free Tire Leader

FLAT FREE WHEELS

#1 Brand for Premium, Polyurethane Flat Free Tires

Wheelbarrow & Cart Wheels



46G089



46G090



46G091



46G096



46G097



46G098



46G099

Trailer, Cart & Lawn Mower Wheels



46G084



46G085



46G092



46G093



46G094



46G095

Hand Truck, Caster & Material Handling Wheels



46G080



46G081



46G082



46G083



46G086



46G087



46G088

- Solid, durable polyurethane foam
- Tires will not go flat!
- Bounce and cushion like an air-filled tire

- Non-Marking
- Various tread, hub & bearing sizes
- Heavy-duty steel ball bearings

Grainger #	Tire Size	O.D.	Width	Tread	Bearing	Hub	Hub Type
46G080	6 x 2"	6.24"	1.97"	Sawtooth	1/2"	2.36"	Center
46G081	8 x 2"	7.99"	6.09"	Sawtooth	1/2"	2.36"	Center
46G082	2.80/2.50-4"	8.58"	3.01"	Sawtooth	5/8"	2.23"	Offset
46G083	2.80/2.50-4"	8.62"	2.99"	Sawtooth	1/2"	2.95"	Center
46G084	9 x 3.50-4"	9.13"	3.16"	Smooth	3/4"	4.02"	Center
46G085	4.10/3.50-4"	10.41"	3.38"	Sawtooth	5/8"	3.51"	Center
46G086	4.10/3.50-4"	10.30"	3.39"	Sawtooth	3/4"	3.51"	Center
46G087	4.10/3.50-4"	12.51"	3.97"	Sawtooth	3/4"	3.02"	Center
46G088	4.10/3.50-4"	12.59"	3.94"	Sawtooth	3/4"	4.51"	Center
46G089	3.50/2.50-8"	13.33"	3.23"	Ribbed	5/8"	3.05"	Center
46G090	3.50/2.50-8"	13.25"	3.17"	Ribbed	3/4"	3.02"	Center
46G091	3.50/2.50-8"	13.23"	3.23"	Ribbed	5/8"	5.99"	Center
46G092	13 x 5.00-6"	13.28"	4.42"	Turf	3/4"	3.02"	Center
46G093	13 x 6.50-6"	13.53"	6.23"	Turf	3/4"	3.01"	Center
46G094	15 x 6.50-6"	13.84"	6.16"	Turf	3/4"	2.99"	Center
46G095	4.80/4.00-8"	15.36"	3.73"	Ribbed	5/8"	3.01"	Center
46G096	4.80/4.00-8"	15.56"	3.44"	Ribbed	5/8"	5.98"	Center
46G097	4.80/4.00-8"	15.38"	3.76"	Ribbed	3/4"	3.01"	Center
46G098	4.80/4.00-8"	15.55"	3.70"	Knobby	5/8"	5.98"	Center
46G099	4.80/4.00-8"	15.58"	3.73"	Knobby	3/4"	3.01"	Center

How to Measure a Tire



Tire Diameter



Tire Width



Hub Length



Bearing Size

marathon

NEWLY AVAILABLE FLAT FREE WHEELS!

America's Flat Free Tire Leader

#36LE96



4.80/4.00-8"
Smooth Tread
6" hub, 1" bushings

#36LE95



4.10/3.50-4"
2-Pack Low Profile
2.25" offset hub,
5/8" bearings

#36LE94



4.10/3.50-4"
Light Weight
2.25" offset hub,
5/8" bearings

#38ER67



2.80/2.50-4"
3" hub, 5/8" bearings
.....
2.80/2.50-4"
3" hub, 3/4" bearings

#38ER15



4.10/3.50-4"
4" hub, 3/4" bearings
.....
4.10/3.50-4"
4" hub, 5/8" bearings

#38ER66

#38ER14

#35NC08



20 x 2.0"
Cart Tire
3/4" bearings

#38ER70



4.80/4.00-8"
Heavy Duty
3" hub, 3/4" bearings

#38ER71



2 Pack
1" bushings

#38ER63



8" Swivel Caster
.....
8" Rigid Caster

#38ER64



10" Rigid Caster
.....
10" Swivel Caster

#38ER62

#38ER65

For more information contact your Grainger Representative or visit Grainger.com®.

AVAILABLE THROUGH

GRAINGER
||| FOR THE ONES WHO GET IT DONE

8SSP6386