

PolyTac™ LED Tactical Light

FL 1 STANDARD	POLYTAC LED
	130 LUMENS
	3h
	144m
	5200 cd



Compact and lightweight, the Streamlight PolyTac LED is a lithium-powered flashlight with super-bright C4® LED technology. A tail-cap switch facilitates single-handed operation. Durable, waterproof construction ensures continued use in many different extreme conditions.

Case Material: High impact super tough nylon polymer for exceptional durability and a sure grip. All openings o-ring sealed for weather resistance. Available in black, coyote or yellow.

Dimensions: Length: 5.22 in. (13.3 cm) Major Diameter: 1.25 in. (3.18 cm) Body Diameter: 1.00 in. (2.54 cm)

Weight: 4.1 oz (116 grams)*

Lens: Borofloat glass lens, o-ring sealed.

Light Source: C4 LED technology, impervious to shock with a 50,000 hour lifetime.

On/Off: Tailcap push button provides one handed momentary or constant “on” operation.

Battery: Two CR123A lithium batteries

Features:

- LED Solid State Power Regulation provides maximum light output throughout battery life
- IPX7 rated design; waterproof to 1 meter for 30 minutes.

Approvals: Most models meet applicable European Community Directives meets requirements of NFPA 1971-8.6 (2007)

Warranty: Streamlight warrants this product to be free of defect for a lifetime of use. We will repair, replace or refund the purchase price, at our option, of any Streamlight product that does not work or that you manage to break for as long as you own it. Of course, this limited lifetime warranty excludes abuse, batteries and bulbs.

**With batteries (included in purchase).*

Item		UPC	Part #
PolyTac LED with lithium batteries. Blister Packaged.	Black	080926-88850-0	88850
PolyTac LED with lithium batteries. Blister Packaged.	Coyote	080926-88851-7	88851
PolyTac LED with lithium batteries. Blister Packaged.	Yellow	080926-88853-1	88853





Helmet not included



Item		UPC	Part #
Nylon holster		080926-85905	85905
Deluxe nylon holster		080926-85909	85909
Flip Lens	Red	080926-69115-5	69115
Flip Lens	Blue	080926-69116-2	69116
Flip Lens	Green	080926-69117-9	69117
Flip Lens	IR	080926-69118-6	69118
Rubber helmet strap		080926-99075-3	99075
Black Jack helmet mount		080926-88855-5	88855
Lithium batteries (2) Pack		080926-85175-7	85175
Lithium batteries (12) Pack		080926-85177-1	85177
Lithium batteries (400) Pack		080926-85179-5	85179
Lithium batteries (6) Pack		080926-85180-1	85180

