


Sheet Metal Nibbler

90
55


- > for cutting iron, copper or aluminum plate up to max. 3/64" (1.2 mm) thickness, plastic up to max. 5/64" (2.0 mm) thickness
- > materials are cut without deformation
- > clean cut edges
- > with chip breaker
- > easy handling
- > cutting width: 7/64" (2.7 mm)
- > tool body: special tool steel, rolled, oil-hardened
- > blades: special tool steel, oil-hardened, interchangeable



Notching and chip breaking in a single pass





Notching without chip breaking



90 55 280


WARNING: This product can expose you to chemicals including Nickel, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov


| Product Number | Packaging | ↔ Inch mm |  | Tool | Handles | ⚖ lbs |
|----------------|---------------------------|-----------------|---|---------------|-----------------------|----------|
| 90 55 280 | | 11 280 |  | nickel plated | multi-component grips | 1.02 |
| 90 59 280 | Spare blade for 90 55 280 | | | | | |

Notching Pliers



90
61

- > special pliers for notching out recesses in plastic ledges and plastic casing boxes for electric and sanitary installation
- > notches can be enlarged by initial and final cut
- > clean cut edges
- > easy handling
- > with opening spring, opening limiter and locking lever
- > pliers body: special tool steel, rolled, oil-hardened



90 61 20
 (PATENTED)

The KNIPEX Notching Pliers produce the most common notches in plastic ledges and cable ducts in a simple, fast and clean way. No time-consuming sawing out or nibbling and no additional work required.

| Product Number | Packaging | ↔ Inch mm |  | Pliers | Handles | Capacity | ⚖ lbs |
|----------------|-----------|-----------------|---|-----------|---------------|-----------------------------------|----------|
| 90 61 16 | | 10 250 |  | burnished | plastic grips | 5/8 x 1 1/4 Inch 16 x 32 mm | 0.89 |
| 90 61 20 | | 10 250 | | | | 25/32 x 1 9/64 Inch 20 x 29 mm | 0.91 |