

FM1400HD SERIES

FIBERGLASS TWIN FRONT LADDER

PRODUCT FEATURES















- 1 SHOX™—superior impact absorption
- 2 DaBoot™—Strength, durability and rail surface protection. Patent #7,000,731 B2
- 3 Heavy gauge steel hinges
- 4 Inside spreader braces
- 5 Heavy duty gusset bracing
- 6 Riveted step construction

					APPROX.	
MODEL	LADDER SIZE	STEP Depth	BOTTOM WIDTH	APPROX. SPREAD	WT. (LBS)	APPROX. CUBES
					. ,	
FM1404HD	4′	3"	19 % ₁₆ "	37 1/2"	21	4.7′
FM1405HD	5′	3"	21 1/16"	44 1/8"	24	6.5′
FM1406HD	6′	3"	22 % "	52 ⁵ / ₁₆ "	27	8.3′
FM1407HD	7′	3"	24 1/16"	59 ¹¹/ ₁₆ "	32	10.2′
FM1408HD	8′	3"	25 ¾ ₁₆ "	67 ½"	36	12.4′
FM1410HD	10′	3"	28 % "	81 15/16"	55	17.5′
FM1412HD	12′	3"	31 % "	96 ¾″	68	23.2'
FM1414HD*	14′	3"	34 ⁹ / ₁₆ "	111 1/2"	84	27.5′
FM1416HD*	16′	3"	37 ⁹ / ₁₆ "	126 5/16"	100	33.5′

*Special duty: manufacturer tested to 375 lbs. BOTH SIDES of twin front ladders can be used simultaneously by one person plus materials.

Therefore the duty rating for this ladder is PER SIDE.