Product data sheet Characteristics

RXM3AB1BD

Harmony, Miniature plug-in relay, 10 A, 3 CO, with lockable test button, 24 V DC





Main

Range of Product	Harmony Electromechanical Relays
Series name	Miniature
Product or Component Type	Plug-in relay
Device short name	RXM
Contacts type and composition	3 C/O
[Uc] control circuit voltage	24 V DC
[Ithe] conventional enclosed thermal current	10 A -40131 °F (-4055 °C)
Status LED	Without
Control Type	Lockable test button
Utilisation coefficient	20 %

Complementary

Shape of pin	Flat
[Ui] rated insulation voltage	250 V IEC
	300 V CSA 300 V UL
[Uimp] rated impulse withstand voltage	4 kV 1.2/50 μs
Contacts material	AgNi
[le] rated operational current	10 A 28 V DC) NO IEC
	10 A 250 V AC) NO IEC 5 A 28 V DC) NC IEC
	5 A 250 V AC) NC IEC
	10 A 30 V DC) UL
	10 A 277 V AC) UL
Maximum switching voltage	250 V IEC
Resistive rated load	10 A 250 V AC
	10 A 28 V DC
Maximum switching capacity	2500 VA/280 W
Minimum switching capacity	170 mW 10 mA, 17 V
Operating rate	<= 1200 cycles/hour under load
	<= 18000 cycles/hour no-load
Mechanical durability	10000000 cycles
Electrical durability	100000 cycles resistive
Average coil consumption in W	0.9 W
Drop-out voltage threshold	>= 0.1 Uc
Operate time	20 ms
Release time	20 ms
Average coil resistance	650 Ohm 20 °C +/- 10 %
Rated operational voltage limits	19.226.4 V DC
Safety reliability data	B10d = 100000
Protection category	RTI
Test levels	Level A
Operating position	Any position
CAD overall height	3.26 in (82.8 mm)
CAD overall depth	3.16 in (80.35 mm)


Net Weight	0.08 lb(US) (0.037 kg)
Device presentation	Complete product
Environment	
Environment Dielectric strength	1300 V AC between contacts with micro disconnection
Diction ducingui	2000 V AC between coil and contact 2000 V AC between poles
Product Certifications	CSA
Standards	CE UL
	Lloyd's
	GOST
	EN/IEC 61810-1 CSA C22.2 No 14
	UL 508
Ambient Air Temperature for Storage	-40185 °F (-4085 °C)
Ambient air temperature for operation	-40131 °F (-4055 °C)
Vibration resistance	3 gn +/- 1 mm 10150 Hz)5 cycles in operation 5 gn +/- 1 mm 10150 Hz)5 cycles not operating
IP degree of protection	IP40 conforming to EN/IEC 60529
Shock resistance	10 gnin operation 30 gnnot operating
Pollution degree	2
Ordering and shipping details	
Category	21127 - ZELIO ICE CUBE RELAYS
Discount Schedule	CP2
GTIN	3389119403559
Nbr. of units in pkg.	1
Package weight(Lbs)	1.34 oz (38 g)
Returnability	Yes
Country of origin	CN
Dandelin a Haite	
Packing Units Unit Type of Package 1	PCE
Package 1 Height	1.61 in (41 mm)
Package 1 Length	0.83 in (21 mm)
Package 1 Length	1.10 in (28 mm)
Offer Sustainability	
Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh Regulation	☑ REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Ğ Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific

Warranty 18 months


Product data sheet Dimensions Drawings

RXM3AB1BD


Dimensions




Pin Side View



Wiring Diagram





Symbols shown in blue correspond to Nema marking.


Product data sheet Performance Curves

RXM3AB1BD

Electrical Durability of Contacts

Durability (inductive load) = durability (resistive load) x reduction coefficient.

Resistive AC load



X Switching capacity (kVA)

Y Durability (Number of operating cycles)


A RXM2AB•••

B RXM3AB•••

C RXM4AB•••


D RXM4GB•••

Reduction coefficient for inductive AC load (depending on power factor $\cos \phi$)



Y Reduction coefficient (A)

Maximum switching capacity on resistive DC load



X Voltage DC

Y Current DC

A RXM2AB•••

B RXM3AB•••

C RXM4AB•••

D RXM4GB•••

Note: These are typical curves, actual durability depends on load, environment, duty cycle, etc.