


### Old Design



### New Design

Side View



Top View



Front View



Padlockable locking bar to eliminate the use of 8 keys

### 60"W Mobile Double Shift Bench Cabinet with 8 Drawers (4,000 lbs. Capacity)

- 14 gauge all welded steel
- Full extension drawers each have 250 lbs. capacity
- Drawers move smoothly on ball bearing slides
- Interior cabinet is 26 x 13-7/16 x 24-3/4
- Locking hinge allows all drawers to be locked at once
- 14 gauge fixed shelf

- Low profile lock on cabinet storage spaces, come complete with 2 keys
- Sturdy tubular handle aids in mobility
- 6" x 2" phenolic bolt-on casters:  
(2) swivel and (2) rigid
- Ships fully assembled
- Durable, textured, gray powder coat finish

FOB TX

Model	Overall Dim: WxDxH (In.)	No & Size of drawers: WxDxH (In.)	Ship Wt.
1TGL7	60* x 32-1/8 x 33-7/8 <small>66-3/8" including handle</small>	(4) 29-9/16 x 14-1/8 x 4 (2) 29-9/16 x 14-1/8 x 6 (2) 29-9/16 x 14-1/8 x 8	494 lbs.

- Can be used as a double shift cart
- Better balance
- Improved stability
- Storage space is better distributed

**Unit now has 23.3%  
more storage space**