



12	END CAP	STEEL C12L14, ZINC PHOS COAT
11	END CAP SEAL	PTFE
10	BALL	STEEL C12L14, CHROME PLT.
9	BALL SEAT	CARBON/GLASS FILLED PTFE
8	HANDLE COVER	VINYL
8	HANDLE	STEEL, ZINC PLATE
7	NUT	STEEL, ZINC PLATE
6	SPRING WASHER	STEEL, ZINC PLATE
5	FOLLOWER	STAINLESS STEEL, 304
4	STEM SEAL	CARBON/GLYPHITE FILLED PTFE
3	THRUSTWASHER	CARBON/GLYPHITE FILLED PTFE
2	STEM	STEEL C12L14, NICKEL PLT.
1	BOUY	STEEL C12L14, ZINC PHOS COAT
ITEM	PART NAME	MATERIAL

CATALOG NO.	DIMENSIONS						THREAD SAE J1926	PRESSURE RATING	C _v	WT. LBS.
	A	B	C	D	E	F				
VLE2.NK 1/4	.40	2.01	1.00	3.78	1.63	.53	-4 SAE 7/16-20UNF	3000 CWP 150 SWP	6	.6
VLE2.NK 3/8	.40	2.01	1.00	3.78	1.63	.53	-6 SAE 9/16-18UNF	3000 CWP 150 SWP	12	.6
VLE2.NK 1/2	.50	2.84	1.45	4.78	2.16	.81	-8 SAE 3/4-16UNF	3000 CWP 150 SWP	19	1.5
VLE2.NK 3/4	.75	3.71	2.05	4.78	2.35	.94	-12 SAE 1 1/16-12UN	3000 CWP 150 SWP	34	2.4
VLE2.NK 1	1.00	4.15	2.27	6.10	2.85	1.25	-16 SAE 1 5/16-12UN	3000 CWP 150 SWP	54	5.3

UNCONTROLLED DRAWING

THIS PRINT IS THE PROPERTY OF DYNAGUIP CONTROLS AND SHALL NOT BE COPIED, REPRODUCED, LOANED, OR DISPOSED OF DIRECTLY OR INDIRECTLY, NOR USED FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT IS SPECIFICALLY FURNISHED EXCEPT BY WRITTEN PERMISSION OF DYNAGUIP CONTROLS.

NO. VLE2.NK FILE NO. SUB086

TITLE
BALL VALVE - VLE SERIES
SAE O-RING BOSS

DR	DATE	CHK'D	DATE	ENGR	DATE
TAP	11-15-00	LJH	10-24-97	LJH	10-24-97

