

RUST BREAKER® PENETRANT



LU™103



Light Pressure Lubricant



NSF® Registered; H2 Rated (Lubricants with no contact) (Registration # 127526)



Dielectric strength value: 47,400 Volts



Minimum - Maximum operational temperature range: Low -20 °F (-29 °C) • High 550 °F (288 °C)



Flash Point: 205 °F (96 °C)



HMIS Hazard Rating: Health (2) • Flammability (0) • Reactivity (0)

- Non-flammable propellant
- Will not harm painted surfaces
- Loosens rust and frozen parts
- Fast penetration



PRESERVE. PROTECT. PREVENT.™

Sprayon® LU™103 Rust Breaker® Penetrant is a fast-acting product that quickly loosens rust while penetrating grease and dirt. A transparent, non staining oil, its light film displaces moisture and acts as a corrosion preventative. Jet stream sprays up to two feet for safe, accurate application. It is a one coat rust and corrosion preventive compound. Pleasant vanilla scent.

LUBRICANTS

USES

- Release rusted or frozen lugs and bolts
- Repair work
- General overhaul
- For use on phosphated or non-phosphated machined parts
- Automotive parts
- Crank shafts
- Other metal components

APPLICATION

Maximum performance is achieved when the metal surfaces to be protected are clean, dry and free of rust, oil and mill scale. Product should be sprayed in a well ventilated area. Sprays best at room temperature (70°F.). Shake well before using. Spray at a distance of 10" to 12" from surface.

PERFORMANCE

DIELECTRIC STRENGTH: 47,400 volts

PLASTIC SAFE: Yes

TEMPERATURE RANGE:

LOW: -20°F

HIGH: 550°F

LOAD CAPACITY: Low

SALT SPRAY CORROSION

(ASTM B-117): will withstand over 120 hrs.

HUMIDITY CABINET TEST

(ASTM D-1748): 2,000 hours minimum

- NSF Registration Number: 115050, H2 Rated
- Penetrant
- Water-Displacer
- Rust Inhibitor
- Non-flammable propellant
- Equipped with SPRAY ANYWAY™ valve and extension tube
- Jet stream spray for safe accurate application
- Active water displacing, creep, and penetrating properties

PACKAGING

Stock #: S00103

UPC Code: 0-75577-90103-6

Fill Wt.: 10 oz.

Per Case: 12

Carton Dimensions:

L 10-7/8" x W 8-3/16" x H 8"

PROPERTIES

APPEARANCE: Light amber

ODOR: Vanilla

PROPELLANT: CO2

WT./GAL.: 6.68

SPECIFIC GRAVITY: 0.80

PAINTABLE: No

H.A.P.S. (Hazardous Air Pollutants): No

SARA 313 Chemicals: No

PROP 65: No

% VOC AEROSOL: 85%

V.O.C. COMPLIANT CALIFORNIA: Yes

V.O.C. COMPLIANT OTC STATES: Yes

FLAMMABLE: Yes

FLASH POINT: >200°F

HAZARD RATING: 2,4,0;

SHELF LIFE: 3 years from date of manufacture

SHIPPING

Refer to section 14 of the material safety data sheet for proper transport information and labeling.

RESOURCES

MSDS/EDS/PRODUCT DATA SHEETS:

sprayon.com

CUSTOMER SERVICE:


1-800-777-2966

TECHNICAL INFORMATION:

1-800-251-2486



LU103



© 2010 Sprayon® Products Made in U.S.A.

Distributed by:

PRESERVE. PROTECT. PREVENT.



Sprayon® Products

101 Prospect Ave. NW
Cleveland, OH 44115
Sprayon.com
1-800-777-2966

310-PDS-LU103