RPF2AP7

Harmony, Power relay, DIN rail/panel mount relay, 30 A, 2 NO, 230 V AC



Main Range of Product Harmony Electromechanical Relays Series name Power Product or Component DIN rail/panel mount relay Type Device short name **RPF** Contacts type and 2 NO composition [Uc] control circuit 230 V AC 50/60 Hz voltage Control Type Without lockable test button Shape of pin Flat Contacts material Silver tin oxide 25 A -40...131 °F (-40...55 °C) relays side by side [Ithe] conventional without a gap enclosed thermal 30 A -40...131 °F (-40...55 °C) 13 mm gap between current two relays 25 A 28 V DC Resistive rated load 30 A 250 V AC

10 %

$\overline{}$										
(:	റ	m	n	lei	m	മ	nt	:а	r۱	1

Complementary			
Mounting Support	Panel DIN rail		
Control circuit voltage limits	184253 V		
[le] rated operational current	30 A 277 V AC) NO UL 20 A 28 V DC) NO UL 30 A 250 V AC) NO IEC 25 A 28 V DC) NO IEC		
[Ui] rated insulation voltage	250 V IEC 300 V UL		
[Uimp] rated impulse withstand voltage	4 kV 1.2/50 μs		
Maximum switching voltage	250 V IEC		
Maximum switching capacity	7500 VA/700 W		
Minimum recommended switching capacity	6000 mW 500 mA / 12 V NO		
Operating rate	<= 1200 cycles/hour under load <= 18000 cycles/hour no-load		
Mechanical durability	5000000 cycles		
Electrical durability	100000 cycles resistive		
Average coil consumption	4 VA 60 Hz		
Drop-out voltage threshold	>= 0.15 Uc		
Operate time	25 ms		
Release time	25 ms		
Average resistance	15600 Ohm at 68 °F (20 °C) +/- 15 %		
Safety reliability data	B10d = 100000		
Protection category	RT II		
Test levels	Level A		
Operating position	Any position		
CAD overall width	1.33 in (33.7 mm)		
CAD overall height	2.70 in (68.5 mm)		
CAD overall depth	1.54 in (39.2 mm)		

Utilisation coefficient

Net Weight	0.18 lb(US) (0.082 kg)		
Device presentation	Complete product		
Environment			
Dielectric strength	2000 V AC between poles with basic 4000 V AC between coil and contact with reinforced 1500 V AC between contacts with micro disconnection		
Standards	CSA C22.2 No 14 EN/IEC 61810-1 UL 508		
Product Certifications	CSA CE GOST UL		
Ambient Air Temperature for Storage	-40185 °F (-4085 °C)		
Ambient air temperature for operation	-40131 °F (-4055 °C)		
Vibration resistance	3 gn +/- 1 mm 10150 Hz)5 cycles in operation 10 gn +/- 1 mm 10150 Hz)5 cycles not operating		
IP degree of protection	IP40 conforming to EN/IEC 60529		
Shock resistance	10 gnin operation 30 gnnot operating		
Pollution degree	3		
Ordering and shipping details Category Discount Schedule	21127 - ZELIO ICE CUBE RELAYS CP2		
GTIN	3389119401579		
Nbr. of units in pkg.	1		
Package weight(Lbs)	3.10 oz (88 g)		
Returnability	Yes		
Country of origin	CN		
Country of origin			
Packing Units			
Unit Type of Package 1	PCE		
Package 1 Height	1.65 in (4.2 cm)		
Package 1 width	2.72 in (6.9 cm)		
Package 1 Length	1.38 in (3.5 cm)		
Unit Type of Package 2	BB1		
Number of Units in Package 2	10		
Package 2 Weight	31.32 oz (888 g)		
Package 2 Height	1.77 in (4.5 cm)		
Package 2 width	5.71 in (14.5 cm)		
Package 2 Length	7.87 in (20 cm)		
Unit Type of Package 3	S02		
Number of Units in Package 3	60		
Package 3 Weight	12.69 lb(US) (5.756 kg)		
Package 3 Height	5.91 in (15 cm)		

11.81 in (30 cm)

15.75 in (40 cm)

Package 3 width

Package 3 Length

Offer Sustainability

Sustainable offer status	Green Premium product		
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov		
REACh Regulation	REACh Declaration		
REACh free of SVHC	Yes		
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)		
Toxic heavy metal free	Yes		
Mercury free	Yes		
RoHS exemption information	₫Yes		
China RoHS Regulation	☑ China RoHS Declaration		
Environmental Disclosure	Product Environmental Profile		


Contractual warranty

Warranty	18	3 months


Product data sheet Dimensions Drawings

RPF2AP7

Dimensions



Wiring Diagram




Symbols shown in blue correspond to Nema marking.

Product data sheet Performance Curves

RPF2AP7

Electrical Durability of Contacts

AC Resistive load




X Switching capacity (kVA)

Y Durability (number of operating cycles)


AC Reduction coefficient for inductive load (depending on power factor cos φ)

Durability (inductive load) = durability (resistive load) x reduction coefficient.



Y reduction coefficient

Maximum switching capacity on DC resistive load



A 30 A

B 25 A

Note: These are typical curves, actual durability depends on load, environment, duty cycle, etc.