Little GIANT®

1-EA-42 SERIES







Features


- For submersible or in-line use
- Epoxy encapsulated motor
- 7' maximum lift
- 36 watts
- 1/4" MNPT discharge
- Thermal overload protection

Construction

- Motor 1/125 HP Epoxy encapsulated
- Maximum Flow Rate 170 GPH @ 1'
- Maximum Head 7'
- Intermittent Liquid Temp up to 120°F
- Intake 1/2" MNPT & 1/4" FNPT
- Discharge 1/4" MNPT
- Housing Glass filled polyester
- Cover Epoxy coated cast aluminum
- Volute Nylon
- Impeller Nylon
- Shaft Seal Viton®
- Electrical 115V, 60 Hz


Dual purpose epoxy encapsulated pump that may be used totally submersed or in-line (fed with pipe of hose). For commercial, industrial and home applications including statuary fountains, water displays, air conditioners, machine tool coolants and many other applications where liquid must be transferred of recirculated. This compact 170 GPH pump features a 1/4" MNPT discharge and 7' shut-off head capability.

1-EA-42 SERIES



Specifications

Model	Item	Discharge	Intake							Performance (GPH@Head)			Shutoff		Cord	Weight
 No.	No.	Size	Size	Listing(s)	HP	Volts	Hertz	Amps	Watts	1'	3'	5'	Ft.	P.S.I.	Length (ft.)	(lbs.)
 1-EA-42	518087	1/4" MNPT	1/2" MNPT & 1/4" FNPT	UL/CSA	1/125	115	60	0.6	36	170	140	100	7	3.0	10	3.17



Replacement Parts

Volute	101377
Impeller	118442
Gasket	131009

PO Box 12010 • Oklahoma City, OK 73157 Phone: 800.701.7894 • Fax: 800.701.8046 E-mail: customerservice@littlegiant.com