

# Fuse Holders for Low-Peak® CUBEFuse®

## Finger-Safe, 1-100A, 600Vac/300Vdc



**Catalog Symbols:** TCFH30N (1-30A)  
 TCFH60N (1-60A)  
 TCFH100N (1-100A)

**Construction:** Finger-safe

**Mounting:** DIN Rail or panel mount

**Ampacities:** TCFH30N - holds any 1-30A CUBEFuse  
 TCFH60N - holds any 1-60A CUBEFuse  
 TCFH100N - holds any 1-100A CUBEFuse

**Voltage Rating:** 600Vac/300Vdc

**Withstand Rating:** 300kA RMS Sym. (UL)  
 200kA RMS Sym. (CSA)  
 100kA DC (UL & CSA)

**Agency Information:**

- UL Listed Fuse Holder: Guide IZLT, File E14853
- CSA Certified Fuse Holder: Class 6225-01, File 47235
- CE compliance for the European Union low voltage directive

**Operating and Storage Temperature Range:** 14 to 149°F(-10 to 65°C)

**Material Specifications:**

- Holder case: Glass filled PBT
- Interface clips: Copper alloy
- Interface clip plating: Tin
- Terminals: Steel
- DIN Rail spring: Stainless steel

**Features and Product Benefits**

- Holder for the world's first finger-safe power fuse system.
- Holder and CUBEFuse together deliver Class CF and Class J fuse performance with dual-element, time-delay and current limiting operation. See Data Sheet 9000 for indicating and non-indicating CUBEFuse performance characteristics.
- Smallest fuse and holder footprint of any class fuse installation including Class J, CC, T and RK.
- DIN Rail or panel mount for easy installation.
- Holders dovetail together to easily achieve the required number of poles.
- All holders (TCFH30N, TCFH60N and TCFH100N) dovetail together to permit mixing ampacities.
- All holders accept equal and lower amp rated TCF\_ indicating and TCF\_RN non-indicating CUBEFuse - no need for a fuse reducer.
- Dual wire rated terminals for wiring ease.
- High 300kA withstand rating stands up to high fault currents.

**Conductors/Wire Range - 75°C Cu Wire Only**

Holder/ Ampacity	No. of Poles*	Single Wire	Dual Wire
TCFH30N	1	18 to 8 AWG	18 to 10 AWG
TCFH60N	1	18 to 4 AWG	18 to 6 AWG
TCFH100N	1	18 to 1 AWG	6 AWG

\* Holders dovetail together to achieve the desired number of poles for the application.


**Carton Quantity and Weight**

Part Number	Carton Qty.	Weight Per Carton	
		lbs	kg
TCFH30N	12	2.42	1.10
TCFH60N	12	2.57	1.17
TCFH100N	6	1.38	0.63

**Terminal Torque Ratings by Conductor and Holder Size (75°C Cu only)**

TCFH30N		TCFH60N		TCFH100N	
Single	Dual	Single	Dual	Single	Dual
10-8 AWG 25lb-in	18-10 AWG 25lb-in	18-10 AWG 20lb-in	18-10 AWG 20lb-in	18-10 AWG 25lb-in	6 AWG 45lb-in
18-12 AWG 20lb-in		8-4 AWG 35lb-in	8-6 AWG 35lb-in	8-1 AWG 40lb-in	

TCFH Dimensions – in (mm)



TCFH30N & TCFH60N

TCFH100N

Holder	A	B	C	D	E	F
TCFH30N	2.30 (58.50)	0.76 (19.37)	1.357 (34.24)	0.15 (3.76)	- -	- -
TCFH60N	2.60 (66.12)	1.03 (26.23)	1.60 (40.64)	0.17 (4.34)	- -	- -
TCFH100N	2.91 (73.81)	1.05 (26.74)	2.01 (50.93)	0.15 (3.81)	0.80 (20.39)	2.51 (63.65)

CUBEFuse Availability and Applications

The indicating Low-Peak® CUBEFuse® (TCF\_) and non-indicating Low-Peak CUBEFuse (TCF\_RN) are available in amp ratings from 1-100A. See Data Sheet 9000. The CUBEFuse is also used in these other Cooper Bussmann® circuit protection solutions.



TCF\_ Indicating and TCF\_RN non-indicating CUBEFuse. Data Sheet 9000



CCP\_CF 1-, 2- & 3-Pole switched disconnects Data Sheet 1157  
 CCPB 1-, 2- & 3-Pole disconnects for the Quik-Spec™ Coordination Panelboard. Data Sheet 1160  
 CF\_ Quik-Spec™ Safety Switch disconnect (optional window). Data Sheet 1156

The only controlled copy of this Data Sheet is the electronic read-only version located on the Cooper Bussmann Network Drive. All other copies of this document are by definition uncontrolled. This bulletin is intended to clearly present comprehensive product data and provide technical information that will help the end user with design applications. Cooper Bussmann reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Cooper Bussmann also reserves the right to change or update, without notice, any technical information contained in this bulletin. Once a product has been selected, it should be tested by the user in all possible applications.