



MCR
SAFETY

9690

Flex Tuff

Dipped

Specification Sheet

PRODUCT DESCRIPTION:

Flex Therm options give you all of the benefits of our Flex Tuff series of gloves, but with the addition of Thermal protection! The 9690 is made of a an acrylic/polyester/cotton string knit shell with a gray latex palm coating. With these gloves you can get a grip on staying warm!

FEATURES:

- Extra thermal protection
- High comfort level
- Allows manual dexterity
- For heavier duty requirements

APPLICATIONS:

Cold storage applications, Commercial fishing, Frozen food packaging, Carpentry, Construction, Landscaping, Mechanics



TECHNICAL DATA FOR: 9690

Series	Flex Tuff	EN 388 : CE Score - Abrasion	2
Material Group	Strings	EN 388 : CE Score - Cut	2
Product Type	Dipped	EN 388 : CE Score - Tear	4
Glove Size	Large	EN 388 : CE Score - Puncture	1
Gauge	10 Gauge	ANSI Cut	ANSI Cut A3
Material	Cotton / Polyester / Acrylic	Conductive Heat Testing	Level 2 (Applications less than 284 degrees F)
Insulated	Insulated		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

9690
Flex Tuff
Dipped
Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
9690L	Large	10.79	6.25	3.62	22.788 lb.	3.798
9690M	Medium	10.55	6.10	3.62	20.574 lb.	3.429
9690S	Small	10.31	5.92	3.62	20.838 lb.	3.473
9690XL	X - Large	11.11	6.49	3.74	20.820 lb.	3.470

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved