CEILING FAN & FIXTURE SUPPORT PRODUCTS

KWIK-BRACE® - New Construction Braces for Lighting Fixtures or Ceiling Fans 1-1/2 in. Depth

A35





Catalog #: 926-1

APPLICATIONS

RACO® KWIK-BRACE® is a heavy-duty ceiling fan brace designed for new or existing construction where joists are accessible

PRODUCT FEATURES

Slides apart to accommodate joist spacing from 16" to 24", screws provided #10-32, 1" long ceiling fan screws provided and #8-32 ceiling fixture mounting provisions Metal protection plate included Nail spurs for easy brace positioning Easy installation, up front ground screw Easy to follow instructions and mounting hardware included

UL LISTED

File E195978

US PATENTS

7,148,420; 6,595,479; 7,191,994

RECOMMENDED MAX LOAD

Ceiling Fan (Dynamic) Lbs., 16 in.

Joist Span:

Joist Span:

Ceiling Fan (Dynamic) Lbs., 24 in. 70

Span:

Fixture (Static) Lbs., 16 in. Joist

Fixture (Static) Lbs., 24 in. Joist Span:

CONFIGURATION

90

Cable Priouts: Drawn or Welded: **INSIDER®** Drawn Raised Ground: Yes Side Knockout(s): Bottom Knockouts(s): (3) 1/2 in.

PRODUCT MEASUREMENTS

1-1/2 in. Depth: Cubic Inches (cm3): 15.8 (258.9) Wt. Ea. (Lbs.): Product Length (in.): 2.054 15.00 Product Width (in.): Product Height (in.): 2.88 4.06

PACKAGING

Minimum Pack Qty.: 12 Std. Pkg.: 12 Product UPC-A Labeled: Weight (Lbs. Per/C): Yes 205.40 Ship Carton Length (in.): Ship Carton Width (in.): 15.50 8.00 Ship Carton Height (in.): 12.25 Ctn Weight (Lbs.): 24.70 Pallet Qty: 432

UPC Number: 050169092613 12of5: 50050169092618