

HIGHEST HOLDING POWER IN THE INDUSTRY

CARTON SEALING TAPES

You place high value on uptime. And, you demand a carton sealing tape that's strong enough to hold and tough enough to endure the rigors of shipping and storage. It's why Shurtape engineers its HP Series carton sealing tapes to the highest standards – to keep your lines running at peak production and to deliver the consistent, reliable seal you demand. So you can be confident your seal will maintain its hold, from the packaging line to the customer.

Constructed of biaxially oriented polypropylene (BOPP) film with a unique hot-melt adhesive formula, Shurtape HP Series carton sealing tapes deliver an instant, strong bond with cartons to keep them secured. HP Series can be used for manual applications using hand rolls or on automated packaging lines where machine-length rolls keep packaging lines running longer and faster. They release smoothly from the roll, offer excellent holding power, and provide the control you demand to maximize packaging line throughput to save time and labor.

No matter your environment or application, HP Series performs reliably down to the core.



OUR LOCATIONS

REGIONAL SALES OFFICES & DISTRIBUTION CENTERS

NORTH CAROLINA

Catawba Industrial Place
3389 Catawba Industrial Place
Catawba, NC 28609

tel: (828) 322-2700
(888) 442-8273
fax: (828) 322-4209

ARIZONA

First Commerce Center
725 N 73rd Avenue, Suite 112
Phoenix, AZ 85043

tel: (623) 463-5886
(800) 342-8273
fax: (623) 463-5809

INTERNATIONAL SALES OFFICES & DISTRIBUTION CENTERS

US CORPORATE HEADQUARTERS

Shurtape Technologies, LLC
1712 8th Street Drive SE
Hickory, NC 28602 USA

tel: (828) 322-2700
(888) 442-8273
fax: (828) 322-4209
www.shurtape.com

CANADA

6685 Kennedy Road, Suite 3
Mississauga, ON
Canada L5T 3A5

tel: (905) 669-0800
fax: (905) 696-8176

EUROPE

Kip GmbH
Schlavenhorst 9 (Industriepark)
D-46395 Bocholt, Germany

tel: +49 2871-23466-27
fax: +49 2871-23466-32
contact: Monica Ptok
www.kip-tape.com

UNITED ARAB EMIRATES

Shurtape Ved Ltd.
Jebel Ali Free Zone
Dubai, United Arab Emirates

tel: +971 (4) 881-3155
fax: +971 (4) 881-3166/883-1974
email: shurtape@emirates.net.ae

MEXICO

Shurtape México, S. de R.L. de C.V.
Paseo de la Constitución #11
Fracc. Ind. Peñuelas
C.P. 76148, Querétaro, QRO
México

tel: +52 (44) 2220-6367
fax: +52 (44) 2220-6366
email: shurtmex@prodigy.net.mx

PERU

Shurtape Perú S.A.
Calle Minería 141
Santa Anita, Lima 43
Peru

tel: +51 (1) 416-3400
fax: +51 (1) 383-0476
email: ventas@shurtapeperu.com

ASIA-PACIFIC

Shurtape Technologies Co., Ltd.
Changshu Southeast Economic
Development Zone
No. 301 Yintong Road, Jiangsu 215500
China

tel: +86 (512) 5235-9500
fax: +86 (512) 5235-9528
email: info@shurtape.com.cn

HP SERIES

SHURTAPE.COM 1.888.442.TAPE

Shurtape
TRUE TO YOUR WORK[®]







SHURTAPE.COM 1.888.442.TAPE    





Shurtape
TRUE TO YOUR WORK[®]


ISO 9001 CERTIFIED QUALITY SYSTEM © 2015 Shurtape Technologies, LLC
Printed in USA on recycled paper. Form #SS-HPSeries-05/04/2015-P1000

A TAPE FOR EVERY CARTON SEALING NEED

CARTON SEALING TAPES

		Tensile	Adhesion to Stainless Steel	Thickness	Holding Power to Fiberboard	Service Temperature Range
HP 100°	 <p>Automated or manual sealing of lightweight cartons</p> <ul style="list-style-type: none"> • Easy unwind • Instant, permanent bond • Application temperature range of 35 F to 110 F 	21 lbs/in width	43 oz/in width	1.6 mils	10,000 min	20 - 150 F
HP 200°	 <p>Automated or manual sealing of medium-weight cartons</p> <ul style="list-style-type: none"> • Superior performance • Instant, permanent bond • Transparent colors for inventory identification • Application temperature range of 35 F to 110 F 	27 lbs/in width	44 oz/in width	1.9 mils	15,000 min	20 - 150 F
HP 300°	 <p>Automated or manual sealing of medium-weight cartons</p> <ul style="list-style-type: none"> • Performance grade • Instant, permanent bond • Application temperature range of 35 F to 110 F 	30 lbs/in width	47 oz/in width	2.2 mils	20,000 min	20 - 150 F
HP 400°	 <p>Automated or manual sealing of large, heavyweight cartons</p> <ul style="list-style-type: none"> • High performance • Instant, permanent bond • Ideal for high-speed, critical-closure production lines • Application temperature range of 35 F to 110 F 	33 lbs/in width	54 oz/in width	2.5 mils	25,000 min	20 - 150 F
HP 500°	 <p>Automated or manual sealing of heavy duty cartons</p> <ul style="list-style-type: none"> • Premium grade • Instant, permanent bond • Ideal for use on demanding packaging lines on cartons with high recycled content • Application temperature range of 35 F to 110 F 	42 lbs/in width	58 oz/in width	3 mils	30,000 min	20 - 150 F
HP 800	 <p>Automated or manual bottom sealing of heavy duty, double- and triple-walled cartons</p> <ul style="list-style-type: none"> • Abrasion resistant polyester film • Meets ASTM D5486, Type II standard • Application temperature range of 35 F to 110 F 	54 lbs/in width	95 oz/in width	3.4 mils	35,000 min	20 - 150 F

		Tensile	Adhesion to Stainless Steel	Thickness	Holding Power to Fiberboard	Service Temperature Range
HP 132°	 <p>Cold temperature sealing of light weight cartons</p> <ul style="list-style-type: none"> • High performance in cold temperature environments • Instant, permanent bond in sub-freezing temperatures • Application temperature range of 20 F to 75 F 	21 lbs/in width	30 oz/in width	1.6 mils	10,000 min	-20 - 100 F
HP 232°	 <p>Cold temperature sealing of light to medium-weight cartons</p> <ul style="list-style-type: none"> • High performance in cold temperature environments • Instant, permanent bond in sub-freezing temperatures • Application temperature range of 20 F to 75 F 	27 lbs/in width	30 oz/in width	1.9 mils	10,000 min	-20 - 100 F
HP 235	 <p>Automated or manual sealing of highly recycled corrugate</p> <ul style="list-style-type: none"> • High holding power on highly recycled or 100% PCW/OCC cartons • Tough, aggressive and consistent case sealing performance • Application temperature range of 35 F to 110 F 	27 lbs/in width	50 oz/in width	2 mils	15,000 min	20 - 150 F
HP 240/250	 <p>Production grade lock printed packaging tape</p> <ul style="list-style-type: none"> • Durable messages won't smear/smudge or degrade adhesive • HP 240 comes in standard messages • HP 250 offers custom messages with adequate lead times and minimum orders • Application temperature range of 35 F to 110 F 	27 lbs/in width	44 oz/in width	1.9 mils	15,000 min	20 - 150 F



TIME TO UPGRADE YOUR TAPE APPLICATORS?

If you demand packaging equipment that will help you achieve efficiency on the line, as well as produce a quality seal you can rely on...look no further than The ShurSEAL® Solution.

A packaging solution combining Shurtape HP Series carton sealing tape with a PrimeLoc™ tape applicator*, The ShurSEAL Solution is engineered for better performance and efficiency – producing a consistent and secure seal, every time.

In addition to excellent holding power from Shurtape HP Series carton sealing tapes, the PrimeLoc tape applicators offer innovative design features, including unmatched wipe-down force for tamper-evident seals and an edge-folding option for a no-knife opening feature.

Contact your Shurtape sales representative for more information.

*Shurtape® is an authorized distributor of PrimeLoc™ Packaging, Inc. PrimeLoc™ is a trademark of PrimeLoc Packaging, Inc.