

SHOWA
8113C

Light weight yet highly cut-resistant, SHOWA 8113C is constructed with a dotted coating, "stretch" feel, and thermal warmth for the full scope of cut resistance protection.

FEATURES

- 13-gauge seamless Thermax® lined knit with AlphaSan®
- Engineered with HPPE fibers
- Ambidextrous
- PVC dotted on both sides

BENEFITS

- Level A3 ANSI cut-resistance
- Unmatched stretch, comfort and thermal warmth
- PVC dotting provides great grip
- Breathable coating

INDUSTRY



Aerospace



Engineering



Glass



Mechanical

IDEAL APPLICATIONS

- Intricate parts handling
- Mechanical and engineering
- Handling heavy equipment
- Handling glass and windows
- Window manufacturing
- HVAC



TAA PRODUCTS

MADE IN USA

MATERIAL

- Glass Fiber
- HPPE
- Seamless knit


COATING

- PVC dots

GRIP

- Embossed

STANDARDS



SHOWA
8113C



PACKAGING
● 12 Gloves per case



SIZES

- XS
- S
- M
- L
- XL



COLOUR

- light gray w/blue dots



[YOU MIGHT ALSO BE INTERESTED IN

SHOWA
8115



MATERIAL
Glass Fiber
COATING
Uncoated

SHOWA
8110



MATERIAL
Glass Fiber
COATING
Uncoated

SHOWA
8127



MATERIAL
Glass Fiber
COATING
Uncoated

SHOWA
S-TEX 581



MATERIAL
Kevlar
COATING
Foam nitrile

[USER INSTRUCTIONS

Do not use where there are chemical, electrical, thermal or entanglement risks. Wash at 40°C max. Performance levels as per standard EN388 retained after 3 washes, subject to variations linked to actual usage conditions. The performance levels apply to the coated surface only. Store in a dry place, away from the light.

[DISCLAIMER

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment. The manufacturer reserves the right to make any modifications it deems necessary.

Get in touch

SHOWA USA | 579 Edison Street - Menlo, GA 30731, USA

USA@SHOWAGroup.com

© SHOWA Group 2018 | All rights reserved