ADJUSTABLE ALUMINUM GANTRY CRANE - AHA-6-12-12 *** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE *** ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON 12" 126 1/2" 158" 122" MIN 146" MAX 3D VIEW SHOWN FOR REFERENCE ONLY 64 11/16" DIMENSION TOLERANCE ± 1/4" STANDARD FEATURES I. THE UNDERSIGNED, AGREE THAT THE PRODUCT AS SPECIAL FEATURES MODEL NUMBER IS AHA-6-12-12 REPRESENTED SATISFIES DESIGN AND DIMENSION NONE CAPACITY IS 6,000 LBS. REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION Α BASE WIDTH IS 64 11/16" P COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE P MAX OVERALL HEIGHT IS 158" AND LOCAL REGULATIONS AND STANDARDS. R I-BEAM HEIGHT IS 12" ANY MODIFIED UNITS ARE NON-RETURNABLE 0 I-BEAM FLANGE WIDTH IS 7" [] As drawn [] As marked V OVERALL I-BEAM LENGTH IS 144" Signed: Date: USABLE I-BEAM LENGTH IS 120 1/4" ADJUSTABLE UNDER I-BEAM HEIGHT Printed Name: 122" MIN LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING 146" MAX DISTRIBUTOR'S NAME: HEIGHT IS ADJUSTABLE IN 6" INCREMENTS W.O.# X VESTIL MANUFACTURING CASTERS: (4) Ø8" X 3" WIDE PHENOLIC SWIVEL CASTERS WITH FOUR DRAWN BY: ND DATE: 05/21/09 SALES: X LOCKING POSITIONS reference: X CRANE MAY BE TAKEN APART AND BUNDLED WITH SCALE: 1:42 FILE NAME: (2) INCLUDED STRAPS FOR EASY TRANSPORT

ALUMÍNUM CONSTRUCTION

Quoted lead time: $_{
m Y}$

QUOTE #

Χ

28-007-260