




CAT. NO.	CONFIGURATION	RATING	IEC COLOR RATING	UL	CSA
HBL4716C	NEMA L5-15P 	15A 125V	YELLOW	YES	YES
HBL4586C	NEMA L6-15P 	15A 250V	BLUE	YES	YES
HBL4786C	NEMA L7-15P 	15A 277VAC	GRAY	YES	YES

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
BLADE HOLDER	NYLON	NATURAL
RETAINER	POLYCARBONATE	CLEAR
CASING	NYLON	NATURAL
WIRE CLAMPS	.062 CRS	NICKEL PLATE
CONTACT BLADE	.060 BRASS	*
BINDING SCREWS	BRASS	*
GROUND HEX HEAD BINDING SCREW	BRASS	GREEN
MTG. SCREWS	BRASS	NICKEL PLATE
ASSEM FASTENERS	STEEL	ZINC PLATE
CAUTION LABEL	VINYL	YELLOW

DIMENSION SHEET FOR CAT. NO. SEE TABLE



REPAIRABLE

NON-REPAIRABLE

B

M-7147

8



CATALOG NO. HBL4716C (NOT SHOWN TO SCALE)

8	REDRAWN WITH EMBEDDED CAD MODEL WITH NO CHANGES TO PART GEOMETRY. PER DCN 21895 SPN	DJP	2/5/16
REV	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
**INSULGRIP®
 2 POLE 3 WIRE
 GROUNDING TWIST-LOCK®
 FLANGED INLETS**

TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLES = ± 2'	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT			
	DR. BY	RCM	APP. BY	VFL
	TR. BY		SCALE	1:1
	CHK. BY	ZIMM	DATE	7/14/93

NOTES:

1. DIMENSIONS ARE IN INCHES [mm]
2. * WHITE FINISH ON NEUTRAL PARTS WHEN USED