



WORKSAFE VISION RECHARGEABLE

Model#200521

THE BEST IN CLASS HEADLAMP FOR OPTIMAL VISION IS NOW RECHARGEABLE!

- USB Rechargeable - 2.5 Hour Charge Time
- Modes: High Spot, Medium Spot, Low Spot, High Flood, Low Flood, Flash
- Large push button switch
- Lightweight polymer housing
- Adjustable Mount tilts down to see ground or objects below
- Low profile design fits within most visors and shields
- Strap securely adheres to helmets, hardhats and heads.
- IPx4 rated water-resistant design



185 LUMENS ON HIGH OR CHOOSE THE
LOW MODE FOR 100 HOURS OF RUNTIME!

SPECIFICATIONS

POWER SOURCE: Lithium Polymer Battery

LAMP : Advanced LED Technology

WEIGHT: 3.5 oz. with Batteries

LENGTH: 2.4 in. **WIDTH:** 1.4 in. **HEIGHT:** 1.8 in.

COLORS: Hi-Vis Green, Black































SAFETY RATINGS

UL Protection Methods

UL 121201 9TH Ed CSA C22.2

NO. 213-17 3RD Ed

Class I, II, III Div 2 Groups A-G T4

| SPOT HIGH MODE | | SPOT MEDIUM MODE | | SPOT LOW MODE | | FLOOD HIGH MODE | | FLOOD LOW MODE | |
|--|--|---|---|---|--|--|--|---|---|
| FL1 STANDARDS | | FL1 STANDARDS | | FL1 STANDARDS | | FL1 STANDARDS | | FL1 STANDARDS | |
|  185 LUMENS |  6 h |  65 LUMENS |  12 h |  10 LUMENS |  100 h |  60 LUMENS |  6 h |  15 LUMENS |  18 h |
|  1,000 cd |  1m |  320 cd |  1m |  50 cd |  1m |  1,000 cd |  1m |  320 cd |  1m |
|  63m |  |  35m |  |  14m |  |  15m |  |  8m |  |

See it all.™

