

STAINLESS STEEL STRUT CLAMPS




Features:

- Manufactured in type 316 stainless steel to meet any stringent sanitary condition
- Polished with standard "brite" finish to increase corrosion resistance and aesthetic appearance
- Designed for use with 1-5/8" stainless channel
- Type 316 stainless steel nut and bolt included
- No package qty. required

Certifications and Compliances:

- Calbrite stainless steel strut clamps are fabricated to UL standards



Applications:

Used at any point along the slot side of the channel and are inserted into the two channel returns. Designed for use in standard 1-5/8" channels. Supplied with stainless nut and bolt.

Industries Commonly Served:

- Food & Beverage Production & Distribution
- Chemical Plants
- Water & Wastewater Treatment
- Pharmaceuticals & Cosmetics
- Refining & Extraction Sites
- Petrochemical
- Pulp & Paper Mills
- Marine & Coastal Facilities

Part Number	Trade Size	Material Thickness	Design Load (lbs.)	Bolt Size	Weight (ea) per lb.
S60500SC00	1/2"	0.061"	400	1/4-20 x 3/4"	0.10
S60700SC00	3/4"	0.070"	600	1/4-20 x 3/4"	0.14
S61000SC00	1"	0.075"	600	1/4-20 x 3/4"	0.16
S61200SC00	1-1/4"	0.080"	600	1/4-20 x 3/4"	0.20
S61500SC00	1-1/2"	0.095"	800	5/16-18 x 1"	0.26
S62000SC00	2"	0.105"	800	5/16-18 x 1"	0.34
S62500SC00	2-1/2"	0.105"	800	5/16-18 x 1"	0.36
S63000SC00	3"	0.105"	800	5/16-18 x 1"	0.40
S63500SC00	3-1/2"	0.115"	1000	3/8-16 x 1-1/4"	0.54
S64000SC00	4"	0.125"	1000	3/8-16 x 1-1/4"	0.70

*All dimensions are for informational purposes only *Tolerances +/- 5%*

Calbrite™

A PART OF **atkore**
INTERNATIONAL

STAINLESS STEEL EMT STRUT CLAMPS

Features:

- Manufactured in type 316 stainless steel to meet any stringent sanitary condition
- Polished with standard "brite" finish to increase corrosion resistance and aesthetic appearance
- Designed for use with 1-5/8" stainless channel and EMT
- Type 316 stainless steel nut and bolt included
- No package qty. required

Certifications and Compliances:

- Calbrite stainless steel Strut Clamps are fabricated to UL standards

Applications:

Used at any point along the slot side of the channel and are inserted into the two channel returns.

Industries Commonly Served:

- Food & Beverage Production
 - Marine & Coastal Facilities
 - Chemical Plants
- Water & Wastewater Treatment
 - Pharmaceuticals & Cosmetics
 - Refining & Extraction Sites
- Petrochemical Operations
 - Pulp & Paper Mills
 - Along with other corrosive environments

Part Number	Trade Size	Material Thickness	Design Load (lbs.)	Bolt Size	Weight each per lb
S20500SC00	1/2"	0.058"	400	1/4-20 x 3/4"	0.09
S20700SC00	3/4"	0.068"	600	1/4-20 x 3/4"	0.10
S21000SC00	1"	0.078"	600	1/4-20 x 3/4"	0.14
S21200SC00	1-1/4"	0.079"	600	1/4-20 x 3/4"	0.16
S21500SC00	1-1/2"	0.104"	800	5/16-18 x 1"	0.26
S22000SC00	2"	0.105"	800	5/16-18 x 1"	0.32

All dimensions are for informational purposes only *Tolerances +/- 5%

Calbrite Stainless Steel Conduit Systems

6451 Northwind Pkwy Hobart, IN 46342 • (P) 219.844.6800 • (F) 219.844.6884 • calbrite.com