

STAINLESS STEEL BEAM CLAMPS




Features:

- Manufactured in type 316 stainless steel to meet any stringent sanitary condition
- Polished with standard "brite" finish to increase corrosion resistance and aesthetic appearance
- Type 316 stainless steel set screw included
- No package qty. required

Certifications and Compliances:

- Material: 316SS
- Hardware: 316SS
- Standards: ASTM A351, ASTM F593
- Min. tensile strength is 485 MPa or 70 Ksi



Applications:

This heavy-duty beam clamp is cast in type 316 stainless for superior strength and corrosion resistance. Designed for use to provide a means of attachment to a structural member. Used for hanging conduit or cables from a wall or ceiling. Attachment holes are located on the back and bottom.

Industries Commonly Served:

- Food & Beverage Production & Distribution
- Chemical Plants
- Water & Wastewater Treatment
- Pharmaceuticals & Cosmetics
- Refining & Extraction Sites
- Petrochemical
- Pulp & Paper Mills
- Marine & Coastal Facilities

Part Number	Size	A	Total Jaw Opening	B	C	D	E	F	Load Rating (lbs.)	Weight (ea) per lb.
S60200BC00	1/4"	1/4"-20	1.050"	5/16"-18	1.150"	1.400"	940"	1.280"	150	.19
S60300BC00	3/8"	3/8"-16	1.270"	1/2"-13	1.500"	1.800"	1.810"	1.970"	750	.75
S60500BC00	1/2"	1/2"-13	1.320"	5/8"-11	1.570"	2.000"	2.05"	2.1"	1100	1.25

*All dimensions are for informational purposes only *Tolerances +/- 5%*