

8700 Series

CAFETORIUM CHAIR



BIFMA INTERNATIONAL

ANSI

products meet or exceed applicable ANSI/BIFMA standards

A New *Futuristic Look* in

COLORS

that will bring your Cafetorium to Life!

Introducing...

The Cafetorium Chair

The **Series #8700 Cafetorium Chair** from National Public Seating offers a sleek design with clean lines, in a new futuristic look.

Perfect for cafeteria, auditorium, conference and lecture hall seating, this exciting design will dress up your facility, and is robust enough to last and last.

An upholstered, plush vinyl seat provides comfortable, extended period seating and is matched to a modern-styled polypropylene plastic back that provides ergonomic support. Extremely lightweight at just 10 lbs., its 16-gauge frame provides support where you need it and is built to exceed ANSI BIFMA standards. Store or transport up to 35 chairs in the optional **Model #DY87**, cradle-style dolly. Floor protector glides are made of TPU for sensitive floors, and include built-in gangers for multiple chair setup.

SLEEK POLYPROPYLENE PLASTIC BACK DESIGN PROVIDES ERGONOMIC SUPPORT

MODEL #8721-01-21 SHOWN

SEATING IN COMFORTABLE, PLUSH VINYL

BUILT-IN GANGERS FOR MULTIPLE CHAIR SETUP

NEW PRODUCT FOR 2015

4 IN-STOCK CHOICES



#8704-10-04

#8710-11-10

#8721-01-21

#8742-12-02

MODEL #8710-11-10 SHOWN

FRAMES



BACKS



SEATING (VINYL / FABRIC)



Custom options require only a 6-8 week lead time! MINIMUM: 300 PCS


Customize your Cafetorium Chair with a **Rainbow of Color Options & Combinations!**



Chair Dimensions:
WIDTH 20"
DEPTH 19 1/4"
SEAT HEIGHT 17 1/4"
BACK HEIGHT 30 3/4"

Optional Cradle-style Dolly Available

MODEL #DY87



- DIMENSIONS - 28" L X 18 1/2" W X 26" H
- WEIGHT - 12 1/2" LBS.
- WEIGHT CAPACITY - 350 LBS.
- 7/8" SQUARE TUBING
- 7/8" OD ROUND TUBING
- FRAME FINISH - GREY POWDER COATING

STORAGE OR TRANSPORT - up to 35 chairs high!

CUSTOM COLORS CHOICES FOR COUNTLESS COMBINATIONS

National Public Seating



800.261.4112 | www.nationalpublicseating.com