

# CP 102



## INDUSTRIAL GRADE, MEDIUM-HIGH ADHESION MASKING TAPE

### TYPICAL APPLICATIONS

- For the industrial, commercial and residential paint markets for use on vinyl, metal, glass, plastic and rubber

### PRODUCT FEATURES

- Medium-high adhesion
- Easy to unwind
- Excellent adhesion and quick stick to many surfaces, including irregular shapes
- Removes cleanly from surfaces, leaving clean paint lines
- Good resistance to solvents and heat

### CONSTRUCTION

Overall Grade/Function: Industrial  
Backing: Crepe paper  
Adhesive: Rubber-based

### STANDARD WIDTH(S)

18 mm 24 mm 36 mm 48 mm

### STANDARD LENGTH(S)

55 m  
Contact your Shurtape sales representative for other available sizes

### APPLICABLE STANDARDS

ASTM D 6123/D 6123M-97 (2012), Type I

### COLOR(S)



### PHYSICAL PROPERTIES

	STANDARD	METRIC
Tensile Strength	19 lbs/in width	33.3 N/10 mm
Adhesion to Stainless Steel	32 oz/in width	3.50 N/10 mm
Thickness	5.4 mils	0.14 mm
Elongation	9%	9%
Adhesion to Backing	16 oz/in width	1.75 N/10 mm
Service Temperature Range	50 F to 200 F	10 C to 93 C

Physical and performance characteristics shown above are obtained from tests recommended by PSTC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent a guarantee of product performance. Individual rolls may vary slightly from these averages. The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

### STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

