

CP 106



GENERAL PURPOSE GRADE, MEDIUM-HIGH ADHESION MASKING TAPE

TYPICAL APPLICATIONS

- For packaging, bundling, holding, splicing, masking and labeling applications

PRODUCT FEATURES

- Medium-high adhesion
- Economical, with good performance on multiple surfaces
- Good quick stick and holding power
- Excellent surface contact with enhanced removal properties

CONSTRUCTION

Overall Grade/Function: General purpose

Backing: Crepe paper

Adhesive: Synthetic rubber-based

STANDARD WIDTH(S)

12 mm 18 mm 24 mm 36 mm 48 mm 72 mm

STANDARD LENGTH(S)

55 m

Contact your Shurtape sales representative for other available sizes

APPLICABLE STANDARDS

ASTM D 6123/D 6123M-97 (2012), Type I

STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

COLOR(S)



PHYSICAL PROPERTIES

	STANDARD	METRIC
Tensile Strength	19 lbs/in width	33.2 N/10 mm
Adhesion to Stainless Steel	42 oz/in width	4.6 N/10 mm
Thickness	4.8 mils	0.12 mm
Elongation	8%	8%
Service Temperature Range	60 F to 150 F	16 C to 66 C

Physical and performance characteristics shown above are obtained from tests recommended by PSTC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent a guarantee of product performance. Individual rolls may vary slightly from these averages. The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

