



9672DT5PU

Cut Protection Specification Sheet

PRODUCT DESCRIPTION:

DSM Dyneema® is a high modulus polyethylene (HMPE) fiber available as a continuous filament, spun or engineered fiber (yarn). DSM Dyneema® is 15 times stronger than surgical steel and features excellent abrasion resistance, cut resistance, and comfort. The 9672DT5PU features a 10 gauge blue speckled Dyneema® Diamond Technology shell blended with dual stainless steel, gray PU coated palm and fingers.

FEATURES:

- 10 gauge Blue speckled Dyneema® Diamond Tech 5 shell
- Gray PU coated palm and fingers
- Blended with Dual Stainless Steel
- Sold by the pair


APPLICATIONS:

Aerospace, Automotive , Canning, Foundry, Glass handling, Iron work , Mechanics, Metal fabrication, Millwright operations , Pipe fitting, Sheet metal industry



TECHNICAL DATA FOR: 9672DT5PU

Product Type	Cut Protection	EN 388 : CE Score - Abrasion	4
Glove Size	Large	EN 388 : CE Score - Cut	5
Gauge	10 Gauge	EN 388 : CE Score - Tear	4
Material	Dyneema	EN 388 : CE Score - Puncture	2
		ANSI Cut	ANSI Cut A5





MCR
SAFETY

9672DT5PU

Cut Protection Specification Sheet

Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
9672DT5PUL	Large	9.85	5.24	2.56	26.208 lb.	0.182
9672DT5PUM	Medium	9.64	5.04	2.36	24.048 lb.	0.167
9672DT5PUS	Small	9.05	4.24	2.36	21.312 lb.	0.148
9672DT5PUXL	X - Large	10.44	5.44	2.76	28.800 lb.	0.200
9672DT5PUXXL	XX - Large	0	0	N/A	29.520 lb.	0.205

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved