

## VANTAGE® II HELMET MOUNTED LIGHT

**MARKET**
**APPLICATIONS:** Fire & Rescue, Law Enforcement, Industrial, Security, Public Works & Utilities.

**DESCRIPTION:**

 Lightweight, compact and low profile, the **VANTAGE® II** is available in three versions designed to easily attach above or below full brim Fire Helmets or Slotted Industrial Hard Hat mount or Gallet helmet mounts. The light features the latest in power LED technology combined with an ultra-bright blue LED safety tail light. Powered by a single lithium battery, Sealed for water-resistance.

**CASE MATERIAL:**

6000 series machined aircraft aluminum with black anodized finish.

**DIMENSIONS:**

 Length: 2.37 in. (6.01 cm)      Width: 1.16in. (2.95 cm)  
 Height with Fire helmet clamp: 2.18 in. (5.54 cm) Height with Industrial mount: 1.54 in. (3.91cm)  
 Height with Gallet helmet mount: 1.37 in. (3.47 cm)

**WEIGHT:**

Fire mount 3.65 oz. (103.5 grams) Industrial 2.97 oz. (84.2 grams) Gallet 2.90 oz. (82.21grams) with battery. (Included in purchase)

**LENS:**

High temperature, shock mounted, impact resistant BOROFLOAT® Glass.

**LIGHT SOURCE:**

 C4®LED technology, impervious to shock with a 50,000 hour lifetime.  
 470nm Ultra-bright blue LED safety tail light with a 100,000 hour lifetime.

**LIGHT OUTPUT:**


350 lumens, 3500 candela peak beam intensity, 118 m beam distance and measured system output. The TIR Optic produces a smooth beam hotspot with optimum peripheral illumination to aid in navigation. Optimized electronics provides regulated intensity.

**ON/OFF:**

Large easy access On-Off switch located on rear of light.

**RUN TIME:**

2 hours 15 minutes continuous to 10% of initial lumen output.

**BATTERY:**

Single 3 Volt CR123A lithium battery, with a storage life of 10 years.

**FEATURES:**

 C4®LED technology for extreme brightness.  
 IPX7 rated design; waterproof to 1 meter for 30 minutes.  
 Ultra-bright blue LED safety tail light visible in heavy smoke.  
 Tail light can be configured to flash for industrial and fire applications.  
 Serialized for positive identification.  
 LED Solid State Power Regulation provides maximum light output throughout battery life.  
 1 meter impact resistance tested

**WARRANTY:**

Streamlight's Limited Lifetime Warranty.

**APPROVALS:**


Meets applicable European Community Directives.

Meets requirements of NFPA 1971-8.6 (2013).

**OPTIONAL**
**ACCESSORIES:**

N/A

FL 1 STANDARD	HIGH	LOW
	<b>350</b> LUMENS	<b>135</b> LUMENS
	<b>2h 15m</b>	<b>5h</b>
	<b>118m</b>	<b>80m</b>
	<b>3,500cd</b>	<b>1,700cd</b>

