



**MCR
SAFETY**

6620

**Memphis Redcoat
Supported / Dipped gloves
Specification Sheet**

PRODUCT DESCRIPTION:

The Red Coats are coming! I don't know what code you scream out to say the boss is coming, but they won't have to worry about you working hard in these bad boys. RedCoat® gloves give a snug fit to protect you from harsh chemicals and a sandy finish to help you grip it.

FEATURES:

- Double Dip
- Red
- Seamless PVC
- Treated with ActiFresh
- 10" Length

APPLICATIONS:

Agriculture, Dairy, Farming, Janitorial, Material Handling, Sanitation, Petrochemical industries, Commercial fishing



TECHNICAL DATA FOR: 6620

Series	Memphis Redcoat	EN 388 : CE Score - Abrasion	4
Material Group	Supported	EN 388 : CE Score - Cut	1
Product Type	Supported / Dipped gloves	EN 388 : CE Score - Tear	2
Glove Size	Large	EN 388 : CE Score - Puncture	1
Material	PVC		
Grade	Premium		
Features	Waterproof		
Lining	Seamless shell		
Thumb Style	Wing		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com


©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

6620

Memphis Redcoat Supported / Dipped gloves Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
6620L	Large	9.528	5.905	N/A	29.562 lb.	4.927
6620M	Medium	9.173	5.511	N/A	28.710 lb.	4.785
6620XL	X - Large	9.842	6.260	N/A	30.700 lb.	5.117
6620XXL	XX - Large	10.158	6.575	N/A	33.534 lb.	5.589
6620XXXL	XXX - Large	10.512	7.598	N/A	39.972 lb.	6.662

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved