

AVAILABLE THROUGH

GRAINGER

FOR THE ONES WHO GET IT DONE

GRAINGER.COM® | 1.800.GRAINGER

HONEYWELL BW™ ULTRA MULTI-GAS DETECTOR

Extra Detection. Ultra Protection

At Honeywell, we always put your safety where it should be – first. With Honeywell BW™ Ultra, our new portable five-gas detector, you will be able to do the same for your workers. Designed specifically for sampling and monitoring confined spaces, before and after entry, Honeywell BW™ Ultra has enhanced sensor technology, visibility on gas readings, comfort and connectivity. This makes it the most reliable and user-friendly way to prevent a safety incident.

EXTRA GAS DETECTION. EXTRAORDINARY.

The Honeywell BW™ Ultra complies with all safety regulations in place by detecting your required gases. Furthermore, it goes the extra mile by offering you the option to choose a fifth sensor from a list of gases – for added protection at work.

The Honeywell BW™ Ultra is the first gas detector on the market to feature the 1-Series sensor, with fast response, reliable performance and long life, even in extreme working conditions. That means high accuracy and lower costs.



FEATURES & BENEFITS

Ultra Easy

- Tamper-proof operation with one-button operation
- Intuitive LCD icons for quick decision-making
- Easy service and maintenance

Ultra Visibility

- Intuitive large dot matrix display giving clear readings
- Smart Gas layout for clear sensor reading
- Hole Watch Mode for quick decision-making
- IntelliFlash™ and also Reverse IntelliFlash™ for clear compliance

Ultra Rugged

- Honeycomb-designed housing for extra ruggedness
- Protection designed in the right place
- Scratch-resistant display protector

Ultra Connected


- Honeywell Connected Worker compatible
- Honeywell TouchConnect™ Technology for activating a feature
- Honeywell SafetySuite for unit configuration and reporting

Ultra Comfortable

- Ergonomically designed for easy use
- Light yet rugged design
- Fits in the hand for easy sampling

Ultra Quick

- Quick responding sensor technology
- Quick decision-making because large display
- Quick bump & calibration with IntelliDoX system



AVAILABLE THROUGH

GRAINGER

FOR THE ONES WHO GET IT DONE

GRAINGER.COM® | 1.800.GRAINGER

HONEYWELL ULTRA™ TECHNICAL SPECIFICATIONS

TECHNICAL SPECIFICATIONS	
SIZE	5.8 x 3.3 x 1.6 in. / 14.8 x 8.5 x 4.0 cm
WEIGHT	14.5 oz. / 411 g (with clip)
OPERATING TEMPERATURE	-4 to +131° F / -20 to +50° C
HUMIDITY	5 - 95% RH (non-condensing) continuous
INGRESS PROTECTION	IP66/68
ALARMS AND TYPE	Visual, vibrating, audible (95 dB); Low, High, TWA, STEL, OL (over limit)
SELF-TEST	Activated detectors automatically perform one internal diagnostic test every 24 hours (sensors, battery and circuitry).
TYPICAL BATTERY LIFE	18 hours (14 hours with PID or IR sensor) @ -4° F / -20° C
PUMP DRAW	Sample from up to 75 ft. / 22.9 m
CONNECTED WORKER	<ul style="list-style-type: none"> Bluetooth™ Low Energy (BLE) – Ability to connect to Honeywell's Safety Communicator App Honeywell TouchConnect™ – Easy ability to enter Bump or Calibration mode or change Set-Points
EVENT LOGGING	30 alarm events and 10 bump events
DATA LOGGING	45 days based on 8 hour shifts every 15 seconds logging
USER OPTIONS	<ul style="list-style-type: none"> Adjust STEL period (5-15 minutes in 1-minute intervals) Calibration span levels Calibration interval Bump test interval Select combustible gases measurement: 0-100% LEL (Lower Explosive Limit) or Methane gas 0-5.0% v/v LEL and PID correction factors Calibration due date (1 to 365 days, or set to zero for off) Individual sensor enable/disable Latching alarms Stealth mode Languages: English, French, German, Portuguese, Spanish, Simplified Chinese and Russian
CERTIFICATIONS AND APPROVALS	<p>UL : Class I, Div 1, Group A, B, C, D Class I, Zone 0, Group IIC</p> <p>ATEX: II 1G Ex ia IIC T4 Ga</p> <p>IECEX: Ex ia IIC T4 Ga</p> <p>CE: European Conformity</p> <p>For additional certifications, please review the manual or consult Honeywell Analytics.</p>
WARRANTY	<p>Instrument: 3 years</p> <p>Sensors: 3 years (2 years NH₃, 1 year PID and Cl₂)</p> <p>Battery: 2 years</p>

DUE TO ONGOING RESEARCH AND PRODUCT IMPROVEMENT, SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE.

SENSOR SPECIFICATIONS		
GASES	STANDARD MEASURING RANGE	RESOLUTION
OXYGEN (O ₂)	0-25% vol.	0.1% vol.
COMBUSTIBLE GASES (LEL)	0-100% LEL	1% LEL
COMBUSTIBLE GASES (IR)* LEL - 100% VOL. AUTORANGING	0-100% LEL (0-5.00% vol.) >5% vol.	1% LEL 0.1% vol.
HYDROGEN SULFIDE (H ₂ S)	0-100 ppm	1 ppm / 0.1 ppm
CARBON MONOXIDE (CO)	0-2,000 ppm	1 ppm
CARBON MONOXIDE (LOW H ₂) (CO-H)	0-1,000 ppm	1 ppm
SULFUR DIOXIDE (SO ₂)	0-100 ppm	0.1 ppm
HYDROGEN (H ₂)	0-2,000 ppm	5 ppm
CARBON DIOXIDE (CO ₂)	0-50,000 ppm	100 ppm / 10 ppm
AMMONIA (NH ₃)	0-100 ppm	1 ppm
VOLATILE ORGANIC COMPOUNDS (VOC) **	0-1,000 ppm	1 ppm
CHLORINE (CL ₂)	0-20 ppm	0.1 ppm
NITROGEN DIOXIDE (NO ₂)	0-50 ppm	0.1 ppm
HYDROGEN CYANIDE (HCN)	0-100 ppm	0.1 ppm
NITROGEN MONOXIDE (NO)	0-200 ppm	1 ppm

* Caution – the LEL IR combustible gas sensor option used in Honeywell BW™ Ultra cannot detect certain combustible gases, including hydrogen and acetylene. The application should be reviewed to ensure the Honeywell BW™ Ultra can provide adequate detection. For more information, please contact Honeywell Analytics (www.honeywellanalytics.com).

** Please contact Honeywell Analytics for availability.



INTELLIDOX DOCKING SYSTEM
IntelliDoX combines smart-docking modules with our instrument management system to provide automated testing and record-keeping.

AVAILABLE THROUGH

GRAINGER[®]

||||| FOR THE ONES WHO GET IT DONE

GRAINGER.COM[®] | 1.800.GRAINGER

HONEYWELL ULTRA[™] MULTI-GAS DETECTOR

SKU LIST		
GRAINGER		
ITEM #	HONEYWELL MODEL #	ITEM DESCRIPTION
497A77	HU-X1W1H1M1B1-B-N	BWTM Ultra 5-gas detector (O2, LEL, H2S, CO, CO2, IR), black
497A76	HU-X1W1H1M1B1-Y-N	BWTM Ultra 5-gas detector (O2, LEL, H2S, CO, CO2, IR), yellow
497A72	HU-X1W1H1M1S1-Y-N	BWTM Ultra 5-gas detector (O2, LEL, H2S, CO, SO2), yellow
497A73	HU-X1W1H1M1S1-B-N	BWTM Ultra 5-gas detector (O2, LEL, H2S, CO, SO2), black
497A75	HU-X1W1H1M1Q1-B-N	BWTM Ultra 5-gas detector (O2, LEL, H2S, CO, VOCs), black
497A74	HU-X1W1H1M1Q1-Y-N	BWTM Ultra 5-gas detector (O2, LEL, H2S, CO, VOCs), yellow
497A79	HU-X1W1H1M1A1-B-N	BWTM Ultra 5-gas detector (O2, LEL, H2S, CO, NH3), black
497A78	HU-X1W1H1M1A1-Y-N	BWTM Ultra 5-gas detector (O2, LEL, H2S, CO, NH3), yellow
497A80	DX-ULTRA	Docking Station for Honeywell BW [™] Ultra