

TECHNICAL DATASHEET SERIES 3100 WATERBOSS PIGGYBACK FLOAT




This line of Piggyback Plug float switches closes the circuit when the float switch is in the raised position and has a piggyback plug.

FLOAT SWITCHES

Product Features

Duty:	Pump or Control Duty
Pump Up / Pump Down:	Pump Down (SPST)
Use:	Water, Light Solids
HP Rating:	1/2 HP at 120VAC
Control Duty (min):	200mA @ 12VDC
Conductors	2
Connections:	Piggyback Plug
Temp Rating:	32°F to 140°F
Mercury Free:	Yes
Case Material:	Polypropylene
Field Warranty:	5 Years
Tethered Float:	Yes
Counterweight :	No, Cable Ties Only
Ingress Protection:	IP68
Approvals:	CE
Rotation Sensitive:	No
Max Current (A):	13
Cable Lengths (ft):	10'
Potable Water:	Yes
Cable Insulation:	PVC
Prop 65 Compliant:	Yes
Microswitch :	Honeywell
Microswitch Rating:	1,000,000 Cycles
Ball Type:	Stainless Steel



Part Number	Supply Voltage	Float Cord Length		Plug	Weight Included	Shipping Weight	MAP
	VAC	Feet	Meters				
3100-3	120	10	3	Wire Lead	Yes	1.0	