


# 71 72 460

## Bolt Cutter



- cutting capacity up to 48 HRC hardness
- robust cutting edges are additionally induction hardened, cutting-edge hardness approx. 62 HRC
- forged-in stopper with comfortable shock-absorber
- good access due to very flat construction of head and joint area
- ergonomically angled handles to minimise effort
- sturdy non-slip two-colour dual component handle sleeves
- precise adjustment (12 positions) by eccentric bolt
- high cutting performance with minimum effort due to optimum co-ordination of the cutting edge angle and transmission ratio
- bolted cutter head, replaceable
- blade: chrome vanadium heavy-duty steel, forged, oil-hardened
- joint: special tool steel, forged
- handles: steel tube, powder-coated

<b>Article No.</b>	71 72 460
<b>EAN</b>	4003773066750
<b>Head</b>	grey atramentized
<b>Handles</b>	with multi-component grips
<b>HRC 19 Ø mm</b>	8
<b>HRC 48 Ø mm</b>	5
<b>HRC 40 Ø mm</b>	6
<b>Cutting edge length mm mm</b>	30
<b>Head thickness mm</b>	33
<b>Length mm</b>	460
<b>Net weight g</b>	2100



Forged-in stopper with damping inserts: cushions the cutting stroke comfortably



technical change and errors excepted



### Spare Parts

Article No.	EAN	
71 79 460	4003773066804	Spare cutter head for 71 72 460 complete with screws